

# Definite Purpose Contactors

## Types DP and DPA Class 8910

### Accessories

#### Replacement coils

Type	For use on	Poles	Average consumption (60 Hz)		Basic reference Add code indicating control circuit voltage (1)	Weight kg (lb)
			Inrush	Sealed		
			VA	VA		
Replacement coils	8910 DPA 1●/2●/3●/4●	2 and 3	56	6	9998 DA1 ●●●	–
	8910 DPA ●4	4	109	10	9998 DA2 ●●●	–
	8910 DPA 5●/6●	2 and 3	109	10	9998 DA2 ●●●	–
	8910 DPA 7●/9●	2 and 3	214	19	9998 DA3 ●●●	–

#### Replacement parts kits

Type	Kit description	For use on	Reference	Weight kg (lb)
Replacement parts kits	Contains the necessary movable and stationary contacts, contact springs and additional hardware for one pole	8910 DPA 1●	9998 DRC1	–
		8910 DPA 2●	9998 DRC2	–
		8910 DPA 3●	9998 DRC3	–
		8910 DPA 4●	9998 DRC4	–
		8910 DPA 5●	9998 DRC5	–
		8910 DPA 6●	9998 DRC6	–
		8910 DPA 7●	9998 DRC7	–
		8910 DPA 9●	9998 DRC9	–
		8910 DPA 12●	9998 DRC12	–

#### Miscellaneous parts

Type	For use on	Reference	Weight kg (lb)
DIN mounting adaptor plate	8910 DPA	9999 DMB1	–

(1) Standard control circuit voltage:

Volts	24	110	120	208–240	220	277	440	480	550	600
50 Hz	V14	V02	–	–	V09	–	V06	–	V07	–
60 Hz	V14	–	V02	V09	–	V04	–	V06	–	V07

Example: 9998 DA1 V02.