

Manual Starters and Switches

Accessories and Modifications

Class 2510, 2511, 2512 / Refer to Catalog 2510CT9701

Table 16.22: Accessories—Class 2510 Types F and K

Description	Class & Type	\$ Price
Handle Guard Kit with Padlock Provision ▲	2510FL1	9.50
Emergency Off Actuator	2510PB1	23.70
Additional Key for Key Operated Devices	2510FK1	3.20

▲ Standard on Type K devices.

Table 16.23: Pilot Light Kits—Class 2510 Types F and K

Application	Voltage	Red Pilot Light	Green Pilot Light	\$ Price
		Class & Type	Class & Type	
Type KF, KG, KW ■	110–120 Vac	9999PL11	9999PL11G	47.60
	208–277 Vac	9999PL12	9999PL12G	47.60
	440–600 Vac	9999PL13	9999PL13G	47.60
Type FF or FG, FW ■	115–240 Vac/dc	9999PL10	9999PL10G	28.50

■ Lenses cannot be replaced. Pilot light kits for NEMA 4 Enclosed Units are for replacement purposes only.

Table 16.24: Replacement Nameplates—Class 2510 Types F and K

Description	Application	Nameplate Marking	Nameplate Type Number—Class 2510				\$ Price
			For Type K Switch		For Type F Starter (Includes "Reset" Indication)		
			Without Pilot Light	With Pilot Light	Without Pilot Light	With Pilot Light	
1-3/4" x 2-13/16" Nameplate with Embossed Mounting Holes for #6 Oval Head Screws	Standard commercial switch box cover or flush plate, including Square D stainless steel plates	(Blank) (Special marking – Specify marking desired.)	FN1	—	FN2	—	14.30
			FN5	—	FN6	—	28.50
1-29/32" x 3-27/32" Flat Nameplate with Mounting Holes for #6 Pan Head Screws	Square D NEMA 1 surface mounted enclosure or gray flush plate	(Blank) High Low Forward Reverse (Special marking—Specify marking desired.)	FN10	FN20	FN30	FN40	14.30
			FN11	FN21	FN31	FN41	14.30
			FN12	FN22	FN32	FN42	14.30
			FN13	—	—	—	14.30
			FN14	FN24	—	—	14.30
			FN15	FN25	FN35	FN45	28.50

Table 16.25: Modifications (Types M & T only)

Description	Factory Modifications and Forms		Field Modifications	
	Form Number	Price Addition	Kit Class & Type	\$ Price
Red Pilot Light ♦	P11▲	77.	9999MP1 (110–120 V) 9999MP2 (208–240 V) 9999MP3 (440–600 V)	47.60
Auxiliary Contacts★	X1 (1 N.O.) X2 (1 N.C.)	105.	9999SX11 (N.O.) 9999SX12 (N.C.)	66.00
Jumper Straps ▼	N/A	—	9998SO31	9.50
Contactor only	Y76	No Charge	N/A	—
Electro-polished Finish—N4	G16	add 15%	N/A	—

- ♦ May only be field-added to NEMA 1 enclosures. For green pilot light, order 9999SPG1 additionally.
- ★ For proper operation, only one auxiliary contact kit per device may be added.
- ▼ Used to control a single phase motor utilizing a three phase starter.
- ▲ P11 Pilot Light Voltage Codes:
120 V—V02
200/208 V—V08
230 V—V03
460 V—V06
575 V—V07
The pilot light Form P11 requires a voltage code.
Catalog number example: 2510MBG1V02P11.

Table 16.26: How to Order

To Order Specify:	Catalog Number	
• Class Number	Class	Type
• Type Number	9991	KE1

Contact Kits

See page 16-120 for Class 9998 Replacement Contact Kits.

Table 16.27: Replacement Parts

Description	Class and Type	\$ Price
Replacement Toggle Kits: Type FW and KW (NEMA 4) Type FR and KR (NEMA 7 & 9)	9998HW1	19.50
	9998HR2	20.60
Replacement Handle Kits: NEMA 12 (Ser. B) Type MBA, MCA NEMA 4/4X (Stainless) (Ser. B) Type MBW, MCW NEMA 4/4X (Polyester) Type MBW, MCW NEMA 7 and 9 Type MBR, MCR	9998HWA1	38.00
	9998HWA1	38.00
	9998HR3	38.00
	9998HR3	38.00
Internal Lever	9998IL1	9.50

Table 16.28: Enclosures

For use with Class 2510 Type	Enclosure	Catalog Number	\$ Price
F and K	NEMA 1 Standard	9991EN1	19.50
M—Sizes M0 & M1		9991MG1	38.00
M—Size M1P		9991MG2	38.00
F01, FO1P, FO2, FO2P, FO3, FO3P, FO4, FO4P	NEMA 1 Oversized	9991FE1	28.50
KO1, KO1A, KO1B, KO2, KO2B, KO2C, KO3, KO3A, KO3B, KO4, KO4B, KO4C, KO5, KO5A, KO5B, KO6, KO6B, KO6C	NEMA 1 Oversized	9991KE1	28.50
	NEMA 1 Jumbo	9991KE2	57.00
	NEMA 3R	9991KE3	143.00