

Accessories for Heavy Industrial NEMA Style Controls

Magnetic coils

Replacement a.c. magnetic coils for magnetic contactors and starters

Equipment to be serviced				Frequency	Voltage	Reference	Weight	
Device	Type	NEMA Size or current rating	Number of poles	Hz	V		kg (lb)	
Latch coils for present-design magnetic contactors and starters Classes: 8502, 8536, 8538, 8539, 8702, 8736, 8903, 8910	L	30 A	2 to 6	50	24	9998 L 24	—	
	LX	30 A	2 to 4		110–115	9998 L 44	—	
					120	9998 L 45	—	
					208	9998 L 52	—	
					220	9998 L 53	—	
					240	9998 L 54	—	
					380	9998 L 60	—	
					440	9998 L 62	—	
					480	9998 L 63	—	
					550	9998 L 65	—	
					600	9998 L 66	—	
					60	24	9998 L 23	—
						120	9998 L 44	—
						208	9998 L 50	—
						240	9998 L 53	—
						277	9998 L 55	—
						300	9998 L 56	—
						480	9998 L 62	—
						600	9998 L 65	—
		L	30 A		8 to 12	50	24	9998 LH 24
	LX	30 A	6 to 12	110–115	9998 LH 44		—	
				120	9998 LH 45		—	
				220	9998 LH 53		—	
				240	9998 LH 54		—	
				440	9998 LH 62		—	
				550	9998 LH 65		—	
			60	24	9998 LH 23		—	
				120	9998 LH 44		—	
				208	9998 LH 50		—	
				240	9998 LH 53		—	
				277	9998 LH 55		—	
				480	9998 LH 62	—		
			600	9998 LH 65	—			
	SA (1)	00	All	50	110–115	9998 SAC 45	—	
	Series B				220	9998 SAC 54	—	
					440	9998 SAC 62	—	
					550	9998 SAC 65	—	
			60		24	9998 SAC 23	—	
					120	9998 SAC 45	—	
					208	9998 SAC 52	—	
					240	9998 SAC 54	—	
					277	9998 SAC 55	—	
					380	9998 SAC 59	—	
			480		9998 SAC 62	—		
			600		9998 SAC 65	—		

(1) For use on Type S Series B devices only.