

Accessories for Float Switches

To order, specify the Class and Type number of the kit. Refer to discount schedule CP7G unless otherwise noted.

Table 22.81: Class 9049 Accessories for Float Switches

Description		Applies to Class	Type	\$ Price			
Compensating Spring		9036GG	A13	12.60			
		9038AG	A15	37.50			
		9036DR, DW	A20	10.10			
Float	Dia. 3.62 in. (92 mm), length 4.5 in. (114 mm)	#304 stainless steel	9037E, 9038D	EF1	30.30		
		#316 stainless steel	9037E, 9038D	EF2	75.00		
	Dia. 2.5 in. (64 mm), length 7 in. (178 mm)	#304 stainless steel	9037H, 9038C	HF3	32.60		
		#316 stainless steel	9037H, 9038C	HF4	102.00		
Float Kit	7 in. tapped-at-top #304 stainless steel float, 5 ft rod, 2 stops	Brass rod	All 9036, 9038A	A6	143.00		
		Aluminum rod	All 9036, 9038A	A6A	149.00		
	7 in. center-hole #304 stainless steel float, 5 ft rod, 4 stops	Brass rod	All 9036, 9038A	A6C	168.00		
		Aluminum rod	All 9036, 9038A	A6CA	177.00		
	7 in. center-hole #316 stainless steel float, 5 ft stainless steel rod, 4 stainless steel stops	All 9036, 9038A	A6CS	401.00			
	7 in. tapped-at-top #316 stainless steel float, 5 ft stainless steel rod, 2 stainless steel stops	All 9036, 9038A	A6S	369.00			
	Replacement float—7 in. round center-hole #304 stainless steel	9049A6C, A6CA	AF1	105.00			
Lever	Form R	9036DG	A58	5.30			
Mounting Bracket	Replacing obsolete 9036A with 9036G	9036GG	A54	25.10			
	Replacing 9036A (S or F1) with 9036G	9036GG	A55	30.30			
Rod	Stainless steel	1-3/4 in. long	9037E, 9038D	ER1	12.60		
		2-1/2 in. long	9037E, 9038D	ER2	12.60		
		3-1/4 in. long	9037E, 9038D	ER3	12.60		
		5-1/4 in. long	9037E, 9038D	ER5	12.60		
		7-1/4 in. long	9037E, 9038D	ER7	12.60		
		12-1/4 in. long	9037E, 9038D	ER12	12.60		
		Rod Kit	Additional 2-1/2 ft section with connector	Brass rod	9049A6, A6C	T1	32.60
				Aluminum rod	9049A6A, A6CA	T1A	35.30
Stainless steel rod	9049A6S, A6CS			T1S	81.00		

▲ Refer to discount schedule CP1.

Renewal Parts for Class 9012–9038 Devices

Renewal parts are generally available for Pump Control Products with a numerical date code—for example, 172 (first quarter, 1972)—or a current date code. Parts are no longer available for devices manufactured before 1965.

To order, specify the Class and Type number of the kit. Refer to discount schedule CP7G unless otherwise indicated.

Table 22.82: Class 9998 Renewal Parts Kits for Class 9012–9038 Devices

Description / Equipment To Be Serviced		Parts Kit Type	\$ Price
Actuator Assembly	9012GA, GD, GG, GK, GN, GR 5, 25, 55 Series C only	PC268◆◆	69.00
	9012GA, GD, GG, GK, GN, GR 6, 26, 36, 46, 56 Series C only	PC269◆◆	95.00
	9012GB, GE, GH1, 21, 31, 41, 51; GL, GP, GS1	PC177◆◆	246.00
	9012GB, GE, GH2, 22, 32, 42, 52; GL, GP, GS2	PC178◆◆	246.00
Contact Kit (2-Pole Contacts)	9013FHG22, 29, 32, 39, 52, 59; 9013 FYG; 9036DG, DR, DW; 9037EG, ER, EW, HG, HR, HW30–39; 9038 All Types (2 Kits Required); obsolete 9013HHGY, HSGY; HSWY; 9037HEG, HSG3, 4; 9035DG10, DW10 (This kit also contains a replacement diaphragm for pressure switches. The diaphragm fits pressure switch only.)	PC242★	19.20
	9013GHG, GSG, GHR, GSR, GMG; 9036GG, GR, GW; 9037GG Series C All except Forms H & R; 9016GVG, Form R	PC205	26.60
	9013GHG, GSG, GSR, GMG; 9036GG, GR, GW; 9037GG, GR, GW Series C Form H only; 9016GVG, Form H	PC206	41.00
Diaphragm Assembly	9013GHG, GSG, GHR, GSR, GMG; 9036GR, GW: Series C Form R only; 9016GVG	PC207	41.00
	9012GA, GD, GN, GR1, 21 Series C only	PC265◆◆	75.00
	9012GA, GD, GG, GK, GN, GR 2, 3, 22, 52 Series C only	PC266◆◆	49.20
	9012GA, GD, GG, GK, GN, GR4, 24, 54 Series C only	PC267◆◆	49.20
	Convolute diaphragm assembly for 9013GHG, GSG: Series C	PC208	14.40
Gasket Kit	9013GHW, GSW; and GSW, GHR: Series C	PC211	10.10
	9016 GAW-1, 21	PC233	36.20
Pilot Light, 24 Vdc	Contains all replaceable gaskets for all 9012 open, NEMA 1, 4, 4X, 13 devices	PC184	47.60
	9012, 9016G Forms G7, G8, G9, G10, G21, G22	PC305◆	69.00
Piston Assembly	9012GC, GF, GJ, GQ, GT1, 21, 31, 41, 51 Series C only	PC270◆◆	492.00
	9012GC, GF, GJ, GQ, GT2, 22, 32, 42, 52 Series C only	PC271◆◆	492.00
	9012GC, GF, GQ, GT4, 24, 34, 44, 54 Series C only	PC273◆◆	492.00
Seal Kit	Buna N, for Series A devices: 9037HG/HW/HR30–39; 9038CG/CW/CR31–36	PC337	14.40
	Viton®, for Series A devices with Form Z19 or Z20: 9037HG/HW/HR30–39; 9038CG/CW/CR31–36	PC338	15.80
Seal Tube Kit	Buna N Quad-Ring®, for Series C devices: 9037HG/HW/HR3–12; 9038CG/CW/CR1–6	PC282	43.40
	Viton Quad-Ring, for Series C devices: 9037HG/HW/HR3–12; 9038CG/CW/CR1–6	PC333	43.40
Snap Switch	SPDT, for 9012GA, GB, GC, GD, GE, GF, GG, GH, GJ single pole; except Forms E2, E3, E4, H3: Series C only	PC313◆◆	119.00
	DPDT, for 9012GA, GB, GC, GD, GE, GF, GG, GH, GJ double pole; except Forms E2, E3, H6, H7: Series C only	PC314◆◆	177.00
Switch Mechanism	9036DR1, DW1 Series B	PC285	95.00

◆ If one of these Form designations appears on the pressure switch nameplate, the 9998 PC number must be completed by adding that same Form suffix from page 22-16, and the Form price must be added to the kit price.

◆ Refer to discount schedule CP1.

★ Refer to discount schedule CP7.