

EZ Meter-Pak® Meter Centers and Accessories

Table 2.24: Tenant Circuit Breakers

Poles	Ampere Rating	10 k AIR		22 k AIR		42 k AIR		100 k AIR		
		Cat. No.	\$ Price	Cat. No.	\$ Price	Cat. No.	\$ Price	Cat. No.	\$ Price	
<b>125 A Max. EZM Branch Unit Tenant Circuit Breakers</b>										
2	40	QO240	67.00	QO240VH	146.00	QOH240	317.00	—	—	
	50	QO250	67.00	QO250VH	146.00	QOH250	317.00	—	—	
	60	QO260	67.00	QO260VH	146.00	QOH260	317.00	—	—	
	70	QO270	134.00	QO270VH	224.00	QOH270	528.00	—	—	
	80	QO280	189.00	QO280VH	315.00	QOH280	651.00	—	—	
	90	QO290	189.00	QO290VH	315.00	QOH290	651.00	—	—	
	100	QO2100	189.00	QO2100VH	315.00	QOH2100	651.00	—	—	
	110	QO2110	428.00	QO2110VH	1034.00	QOH2110	1389.00	—	—	
	125	QO2125	428.00	QO2125VH	1034.00	QOH2125	1389.00	—	—	
<b>225 A Max. EZM Branch Unit Tenant Circuit Breakers</b>										
Poles	Ampere Rating	10 k AIR		25 k AIR		65 k AIR		100 k AIR		
		Cat. No.	\$ Price	Cat. No.	\$ Price	Cat. No.	\$ Price	Cat. No.	\$ Price	
2	40	QO240▲	67.00	QO240VH■▲	146.00	QOH240◆▲	317.00	—	—	
	50	QO250▲	67.00	QO250VH■▲	146.00	QOH250◆▲	317.00	—	—	
	60	QO260▲	67.00	QO260VH■▲	146.00	QOH260◆▲	317.00	—	—	
	70	QBP22070TM	474.00	QDP22070TM	1143.00	QGP22070TM	1521.00	QJP22070TM	1890.00	
	80	QBP22080TM	474.00	QDP22080TM	1143.00	QGP22080TM	1521.00	QJP22080TM	1890.00	
	90	QBP22090TM	474.00	QDP22090TM	1143.00	QGP22090TM	1521.00	QJP22090TM	1890.00	
	100	QBP22100TM	474.00	QDP22100TM	1143.00	QGP22100TM	1521.00	QJP22100TM	1890.00	
	110	QBP22110TM	474.00	QDP22110TM	1143.00	QGP22110TM	1521.00	QJP22110TM	1890.00	
	125	QBP22125TM	474.00	QDP22125TM	1143.00	QGP22125TM	1521.00	QJP22125TM	1890.00	
	150	QBP22150TM	474.00	QDP22150TM	1143.00	QGP22150TM	1521.00	QJP22150TM	1890.00	
	175	QBP22175TM	474.00	QDP22175TM	1143.00	QGP22175TM	1521.00	QJP22175TM	1890.00	
	200	QBP22200TM	474.00	QDP22200TM	1143.00	QGP22200TM	1521.00	QJP22200TM	1890.00	
	225	QBP22225TM	474.00	QDP22225TM	1143.00	QGP22225TM	1521.00	QJP22225TM	1890.00	
	3	70	QBP32070TM	1248.00	QDP32070TM	1784.00	QGP32070TM	2442.00	QJP32070TM★	2796.00
		80	QBP32080TM	1248.00	QDP32080TM	1784.00	QGP32080TM	2442.00	QJP32080TM★	2796.00
90		QBP32090TM	1248.00	QDP32090TM	1784.00	QGP32090TM	2442.00	QJP32090TM★	2796.00	
100		QBP32100TM	1248.00	QDP32100TM	1784.00	QGP32100TM	2442.00	QJP32100TM★	2796.00	
110		QBP32110TM	1248.00	QDP32110TM	1784.00	QGP32110TM	2442.00	QJP32110TM★	2796.00	
125		QBP32125TM	1248.00	QDP32125TM	1784.00	QGP32125TM	2442.00	QJP32125TM★	2796.00	
150		QBP32150TM	1248.00	QDP32150TM	1784.00	QGP32150TM	2442.00	QJP32150TM★	2796.00	
175		QBP32175TM	1248.00	QDP32175TM	1784.00	QGP32175TM	2442.00	QJP32175TM★	2796.00	
200		QBP32200TM	1248.00	QDP32200TM	1784.00	QGP32200TM	2442.00	QJP32200TM★	2796.00	
225		QBP32225TM	1248.00	QDP32225TM	1784.00	QGP32225TM	2442.00	QJP32225TM★	2796.00	

▲ Must use EZM125QOA adapter.  
■ QO-VH tenant circuit breaker is rated 22 k AIR max.

◆ QOH tenant circuit breaker is rated 42 k AIR max.  
★ 3-pole QJP tenant circuit breaker is rated 65 k AIR max. at 240/120 Vac, 3Ø4W High Leg Delta, or 100 k AIR max. at 208Y/120 Vac, 3Ø4W.



QO2100VH  
2P, Plug-on Type  
Circuit Breaker



QDP22200TM

Accessories

Table 2.25: Accessories

Accessory	Description	Cat. No.	\$ Price
1200 A Bus Extension (Indoor/Outdoor Cu bus)	1Ø3W Bus Extension (6 in. wide) 1Ø3W Bus Extension (12 in. wide) 3Ø4W Bus Extension (6 in. wide) 3Ø4W Bus Extension (12 in. wide)	EZM1EXT6 EZM1EXT EZM3EXT6 EZM3EXT	767.00 767.00 966.00 966.00
1200 A Bussed Corner Sections (Indoor Cu bus only)	1Ø3W Inside Corner (14.75 in. wide) 1Ø3W Outside Corner (6.20 in. wide) 3Ø4W Inside Corner (14.75 in. wide) 3Ø4W Outside Corner (6.20 in. wide)	EZM1CORNER EZM1ELBOW EZM3CORNER EZM3ELBOW	1788.00 1788.00 2217.00 2217.00
1200 A Transition Sections—Old to New (10.7 in. wide Cu bus)	Add right of old style 1Ø EZM lineup Add right of old style 3Ø EZM lineup Add left of old style 1Ø EZM lineup Add left of old style 3Ø EZM lineup	EZM1TRANR EZM3TRANR EZM1TRANL EZM3TRANL	237.00 252.00 315.00 332.00
Mounting Channel	72" long	EZM72MC	63.00
Secondary Surge Arrester Mounting kit	For use with 1 or 2-SDSA1175 or 1-SDSA3650 (order surge arrester separately)	MMSAMK▼	80.00
Stud Kit for EZM-TB 400–600 A terminal box	Includes (2) 1/2 in.-13 studs per pad and mounting hardware. Four pads per kit. With suffix TBCU only.	EZMSK2	246.00
Al/Cu Lug Kits (Each kit includes three, 2-barrel lugs.)	(1) 1/0–600 kcmil or (2) 1/0–250 kcmil per lug (2) 3/0–500 kcmil per lug (2) 2–600 kcmil per lug	MMLK250 MMLK500 MMLK600	150.00 200.00 233.00
Feed-Thru for EZM-TBCU 800 A Terminal Box	(4) 750 kcmil Al/Cu lugs per phase and neutral. Al wire 600 A max. Cu wire 800 A max.	EZM600FTLK3	480.00
Feed-Thru for EZM-TB 1600 A Terminal Box	(24) additional lugs, 600 kcmil Al/Cu, (6) per phase and neutral.	EZM1600FTLK3	915.00
Fifth jaw Kit	1 per kit	5J▲	18.30
Horn Bypass Kit	Use with Type EZMR 1Ø meter socket only	MMHB	16.70
Slider Type Manual Circuit Closer	For (1) 125–225 A ring-type socket only—indoor/outdoor	MM200MB◊	171.00
Anti-inversion Clip	Rejects 100 A and 200 A watt-hour meters in Class 320 meter sockets in Type EZML branch units.	MMLRK	12.00
QO Adapter for bolt-on Q-frame tenant circuit breakers	For 2P Type QO (40–125 A, 10 kA max. meter center SCCR) or QO-VH and QOH (40–60 A, 100 kA max. meter center SCCR)	EZM125QOA	273.00
DJM Circuit Breaker Alternate Lug (DE2)	Kit includes (3) 2-barrel lugs for (2) 2/0 AWG–350 kcmil Al/Cu or (2) 2/0 AWG–500 kcmil AL per lug.	32510	—
DJM Circuit Breaker Seal Kit	Tamper-evident kit to seal DJM trip dial cover, (1) per circuit breaker, if required. Meets NEC 240-6 [c]	29375	—
Meter Socket Closing Plates	Lexan Closing Plate—EZM, EZMR, EZMH, EZMT Metal Closing plate—EZMR, EZMH, EZML	29007 RSG4	10.10 122.00

Table 2.25: Accessories (continued)

Accessory	Description	Cat. No.	\$ Price
Sealing Rings	Snap-on (Stainless Steel)	ARRP00026	16.70
	Screw-Type (Aluminum)	29008W	20.10
	Latch-Type (Aluminum)—standard	2920910001	8.00
Barrel Lock Kit	For use on ringless EZM or MP branch unit covers, includes 6 each of head protectors, lock nuts and sealing caps. (Barrel lock not included.)	MMBLC	66.00
Tenant Circuit Breaker Filler Plates	125 A Branches—2P Type QO (2 per opening) 225 A Branches—2P and 3P Q-Frame	QOFP EZMPCP	3.60 26.00

▼ Consult your nearest Square D/Schneider Electric sales office for details.  
▲ All sockets include 5th Jaw factory-installed except EZM11\_\_ devices.  
◻ Meter center short circuit current rating is 10,000 RMS symmetrical amperes with manual circuit closers installed (bypass is not designed for use as continuous duty).  
◊ For use on ring type meter sockets only.

Busway Transition Section

EZM busway transition section provides no overcurrent protection for the downstream EZM branch units. Tenant main circuit breakers in these branch units must be selected as “fully rated” equipment. (Examples: QO for 10 kA, QO-VH for 22 kA or QOH for 42 kA.)

Table 2.26: EZM Busway Transition Sections (3Ø only)

Ampere Rating	I-Line® Busway location	Neutral Front	Neutral Back	Width (in.)	\$ Price
1200	RIGHT of EZM Transition Section	EZM3BUSRF	EZM3BUSRB	12.00	2625.00
1200	LEFT of EZM Transition Section	EZM3BUSLF	EZM3BUSLB	12.00	2625.00

