

Table 8.32: Terminal Shrouds for LK Switches

Switch Amperes	Catalog No.	Description
30–60	LK4AP3CN	Shroud Top and Bottom, 3-Pole
100–200	LK4AP33TN	Shroud Top LK4, 3-Pole, 100/200 A
100–200	LK4AP33BN	Shroud Bottom LK4, 3-Pole, 100/200 A
400	LK4AP53TN	Shroud Top LK4, 3-Pole, 400 A
400	LK4AP53BN	Shroud Bottom LK4, 3-Pole, 400 A
600 [4]	LK4AP63N	Shroud Bottom LK4, 3-Pole, 600 A
800–1200 [4]	LK4AP83N	Shroud Bottom LK4, 3-Pole, 800–1200 A

GS2 Fusible Disconnect Switches

Table 8.33: GS Fusible IEC Style Disconnect Switches

Pole	Rating (A)	Catalog No.	Maximum Horsepower Rating				Short Circuit Current Rating 600 Vac		Shaft Style
			240 V	480 V	600 V	250 Vdc	Fuse	SCCR kA	
3	30	GS1DDU3	7.5	15	20	5	CC	100	AG
3	30	GS1DU3	7.5	15	20	5	J	100	AG
3	30	GS2EEU3	7.5	15	20	5	CC	100	B
3	30	GS2EU3N	7.5	15	20	5	J	100	B
3	60	GS2GU3N	15	30	50	10	J	100	B
3	100	GS2JU3N	30	60	75	20	J	200	B
3	200	GS2MU3N	60	125	150	40	J	200	B
3	400	GS2QU3N	125	250	350	50	J	200	B
3	600	GS2SU3	200	500	500	—	J	200	C
3	800	GS2TU3	200	500	500	—	J	200	C



GS2GU3N

Table 8.34: Handles and Shafts for GS Switches [5]

Rating (A)	Handle			Shaft: 12.6 in. (320 mm)	Shaft: 15.7 in. (400 mm)	Shaft Guide	Shaft Style
	Catalog No.	Type	Color	Catalog No.	Catalog No.		
30–60	GS2AH110	1, 3R, 12	Black	GS2AE8	GS2AE81	GS2AEH12	AG
30–60	GS2AH120	1, 3R, 12	Red/Yellow				
30–60	GS2AH410	4, 4X	Black				
30–60	GS2AH420	4, 4X	Red/Yellow	GS2AE2	GS2AE21	GS2AEH12	B
30–400	GS2AH130	1, 3R, 12	Black				
30–400	GS2AH140	1, 3R, 12	Red/Yellow				
30–400	GS2AH430	4, 4X	Black	GS2AE5	GS2AE51	GS2AEH12	C
30–400	GS2AH440	4, 4X	Red/Yellow				
600–800	GS2AH150	4, 4X	Black				
600–800	GS2AH160	4, 4X	Red/Yellow				



GS2AH110



GS2AH130



GS2AH150



Auxiliary Contacts
GS1AD10 + GS2AM110

NOTE: Hole adapter kit for GS1 to GS2 Handles: GS2AH100T0200.

Table 8.35: Auxiliary Contacts for GS Switches [6]

Switch Amperes	Catalog No.	Description
30–800	GS1AM110	Aux Contact 1 N.O.
30–800	GS1AM101	Aux Contact 1 N.C.
30	GS1AD10	Aux Contact Holder

Table 8.36: Shorting Links

For use on:	Shorting Links per Kit	Catalog No.
GS2, 60 A	3	GS1AU203
GS2, 100 A	3	GS1AU303
GS2, 200 A	3	GS1AU403
GS2, 400 A	3	GS1AU503
GS2, 600–800 A	3	GS1AU803



Shorting Links

Table 8.37: NFPA79 Kit

For Use With:	Description	Kit Part Number
GS2Q3N	NFPA 79 Internal Handle Kit 400 A Switch Shaft	GS2AD040N
GS2GU3N, GS2GLU3N, GS2JU3N, GS2JLU3N	NFPA 79 Internal Handle Kit 60–200 A Switch Shaft	GS2AD030N
GS1DDU3, GS1DU3	NFPA 79 Internal Handle Kit for 5 mm Shafts	GS1AD010

Table 8.38: Terminal Shrouds for GS Switches, Line or Load [7]

Switch Amperes	Catalog No.	Description
30–100	—	Standard on product
200	GS2AP43	GS2, 3-Pole, 200 A
400	GS2AP53	GS2, 3-Pole, 400 A
600–800	GS2AP73	GS2, 3-Pole, 600–800 A

[4] 600–1200 A standard with top shroud.

[5] GS2AH100T0200–GS1 to GS2 Handle Adapter if using GS1 holes.

[6] GS1DU3 and GS1DDU3 switches allow up to 4 auxiliary contacts without adding contact holder GS1AD10. For more than 4 contacts, GS1AD10 is required.

[7] Order one terminal shroud per side. For example, order one terminal shroud for either the line side or load side; order two terminal shrouds for both the line side and load side.