

TeSys protection components

Switch-disconnector-fuses
for the North American market,
conforming to UL and CSA standards,
30 to 800 A, TeSys GS. Handles, accessories

530656



GS2 AH●10
GS2 AH●20

530655



GS2 AH●30
GS2 AH●40

4

530654



GS2 AH●50
GS2 AH●60

Handles for external operators

Switch rating	Protection index Nema	Handle colour	Reference	Weight
A				kg
Handles for front-mounted external operators, padlockable				
Door interlock in "I" position (1)				
30 Compact	1, 3R, 12	Black/Grey	GS2 AH110	0.200
		Red/Yellow	GS2 AH120	0.200
30...400	1, 3R, 12	Black/Grey	GS2 AH410	0.200
		Red/Yellow	GS2 AH420	0.200
	1, 3R, 4, 4X, 12	Black/Grey	GS2 AH430	0.240
		Red/Yellow	GS2 AH440	0.240
600 and 800	1, 3R, 12	Black/Grey	GS2 AH150	0.280
		Red/Yellow	GS2 AH160	0.280

Handles for front-mounted external operators with Test facility (2), padlockable

Switch rating	Protection index Nema	Handle colour	Reference	Weight
A				kg
Handles for front-mounted external operators with Test facility (2), padlockable				
Door interlock in "I" position (1)				
30 Compact	1, 3R, 12	Black/Grey	GS2 AHT110	0.200
		Red/Yellow	GS2 AHT120	0.200
	1, 3R, 4, 4X, 12	Black/Grey	GS2 AHT410	0.200
		Red/Yellow	GS2 AHT420	0.240
30...400	1, 3R, 12	Noir/Gris	GS2 AHT130	0.240
		Red/Yellow	GS2 AHT140	0.240
	1, 3R, 4, 4X, 12	Black/Grey	GS2 AHT430	0.240
		Red/Yellow	GS2 AHT440	0.240

Shafts for external operators

Switch rating	Shaft length	Shaft cross section	Reference	Weight
A		mm		kg
30 Compact	200	5 x 5	GS2 AE82	0.100
	320	5 x 5	GS2 AE8	0.125
	400	5 x 5	GS2 AE81	0.150
30...400	200	10 x 10	GS2 AE22	0.160
	320	10 x 10	GS2 AE2	0.280
	400	10 x 10	GS2 AE21	0.320
600 and 800	200	12 x 12	GS2 AE52	0.240
	320	12 x 12	GS2 AE5	0.380
	400	12 x 12	GS2 AE51	0.420

(1) Door interlock override by means of a tool.

(2) The Test position allows testing of the control circuits off-load, by using auxiliary contacts GS1 AM110, GS1 AM101 or GS1 ANT●●. In the "Test" position, the enclosure door can be opened.