



**Schneider Electric USA**  
1415 South Roselle Road  
Palatine, IL 60067  
Customer Care Center: 1-888-778-2733  
Web: [www.schneider-electric.us](http://www.schneider-electric.us)

ALL CATEGORIES > CIRCUIT BREAKERS - THERMAL-MAGNETIC > MOLDED CASE CIRCUIT BREAKERS -  
POWERPACT H-FRAME > I-LINE - 2 POLE MOLDED CASE CIRCUIT BREAKER > ITEM # HJA260701

## ITEM # HJA260701, I-LINE - 2 POLE MOLDED CASE CIRCUIT BREAKER

PowerPact H-frame Thermal Magnetic Circuit Breaker



### Specifications

<b>Fixed AC Magnetic Trip</b>	Hold: 800A - Trip: 1450A
<b>Ampere Rating</b>	70A
<b>General Application</b>	Provides overload and short circuit protection
<b>Approvals</b>	UL Listed - CSA Certified - IEC Rated
<b>For Use With</b>	I-line Panelboards and Switchboards
<b>Voltage Rating</b>	600VAC
<b>Mounting Type</b>	I-Line Plug-On
<b>Weight</b>	5 Pounds
<b>Number of Poles</b>	2-Pole
<b>Phase Connection</b>	AB
<b>Interrupting Rating</b>	100kA at 240VAC - 65kA at 480VAC - 25kA at 600VAC

<b>Terminal Type</b>	I-Line Connection (ON end) - Lugs (OFF end)
<b>Wire Size</b>	#14-3/0 AWG(Al/Cu)
<b>Mounting Height</b>	4.5 Inches