



Schneider Electric USA
1415 South Roselle Road
Palatine, IL 60067
Customer Care Center: 1-888-778-2733
Web: www.schneider-electric.us

ALL CATEGORIES > CIRCUIT BREAKERS - THERMAL-MAGNETIC > MOLDED CASE CIRCUIT BREAKERS -
POWERPACT H-FRAME > I-LINE - 2 POLE MOLDED CASE CIRCUIT BREAKER > ITEM # HJA261501

ITEM # HJA261501, I-LINE - 2 POLE MOLDED CASE CIRCUIT BREAKER

PowerPact H-frame Thermal Magnetic Circuit Breaker



Specifications

Fixed AC Magnetic Trip	Hold: 900A - Trip: 1700A
Ampere Rating	150A
General Application	Provides overload and short circuit protection
Approvals	UL Listed - CSA Certified - IEC Rated
For Use With	I-line Panelboards and Switchboards
Voltage Rating	600VAC
Mounting Type	I-Line Plug-On
Weight	5 Pounds
Number of Poles	2-Pole
Phase Connection	AB
Interrupting Rating	100kA at 240VAC - 65kA at 480VAC - 25kA at 600VAC

Terminal Type	I-Line Connection (ON end) - Lugs (OFF end)
Wire Size	#14-3/0 AWG(Al/Cu)
Mounting Height	4.5 Inches