



30–100 A Compact



100–400 A



GS2AH130



GS2AH150



GS2AH170

LK4 Nonfusible Disconnect Switches

Table 8.28: LK Nonfusible IEC Style Disconnect Switches

Pole	Rating (A)	Catalog No.	Maximum Horsepower Rating				Short Circuit Current Rating 600 Vac		Shaft Style
			240 V	480 V	600 V	250 Vdc	Fuse	SCCR kA	
3	30	LK4DU3CN ^[1]	10	20	30	—	J	100	AL
3	60	LK4GU3CN ^[1]	20	40	50	—	J	100	AL
3	100	LK4JU3CN ^[1]	20	50	50	N/A	J	100	AL
3	100	LK4JU3N	30	75	100	15	J	200	B
3	200	LK4MU3N	75	150	200	15	J	200	B
3	400	LK4QU3N	125	250	350	50	J	200	B
3	600	LK4SU3N	200	400	350	50	J	200	D
3	800	LK4TU3N	200	500	500	—	L	100	D
3	1000	LK4UU3N	200	500	500	—	L	100	D
3	1200	LK4WU3N	200	500	500	—	L	100	D

NOTE: Switches in shaded area are now available as Kits. Please see Table 8.29.

Table 8.29: ^{New!} Kits for Compact Switches LK4: 30, 60 and 100 A

Rating	Kit Catalog Number	Pieces Included ^[2]				
		Compact Switch	400 mm Shaft	Handle Color / Rating	Handle	Guide Cone
30 A	LK4DUKB1	LK4DU3CN	LK4AE41CN	Black / NEMA 1, 12, 3R	LK4AH0110CN	GS2AEH12
30 A	LK4DUKB4	LK4DU3CN	LK4AE41CN	Black / NEMA 4	LK4AH0410CN	GS2AEH12
30 A	LK4DUKR1	LK4DU3CN	LK4AE41CN	Red / NEMA 1, 12, 3R	LK4AH0120CN	GS2AEH12
30 A	LK4DUKR4	LK4DU3CN	LK4AE41CN	Red / NEMA 4	LK4AH0420CN	GS2AEH12
60 A	LK4GUKB1	LK4GU3CN	LK4AE41CN	Black / NEMA 1, 12, 3R	LK4AH0110CN	GS2AEH12
60 A	LK4GUKB4	LK4GU3CN	LK4AE41CN	Black / NEMA 4	LK4AH0410CN	GS2AEH12
60 A	LK4GUKR1	LK4GU3CN	LK4AE41CN	Red / NEMA 1, 12, 3R	LK4AH0120CN	GS2AEH12
60 A	LK4GUKR4	LK4GU3CN	LK4AE41CN	Red / NEMA 4	LK4AH0420CN	GS2AEH12
100 A	LK4JUKB1	LK4JU3CN	LK4AE41CN	Black / NEMA 1, 12, 3R	LK4AH0110CN	GS2AEH12
100 A	LK4JUKB4	LK4JU3CN	LK4AE41CN	Black / NEMA 4	LK4AH0410CN	GS2AEH12
100 A	LK4JUJR1	LK4JU3CN	LK4AE41CN	Red / NEMA 1, 12, 3R	LK4AH0120CN	GS2AEH12
100 A	LK4JUJR4	LK4JU3CN	LK4AE41CN	Red / NEMA 4	LK4AH0420CN	GS2AEH12

Table 8.30: Handles and Shafts for LK Switches

Rating (A)	Handle			Shaft: 12.6 / 320 in. / mm	Shaft: 15.7 / 400 in. / mm	Shaft Guide ^[3]	Shaft Style
	Catalog No.	Type	Color	Catalog No.	Catalog No.	Catalog No.	
30–100	LK4AH110CN ^[1]	1, 3R, 12	Black	LK4AE12CN	—	GS2AEH12	AL
30–100	LK4AH1120CN ^[1]	1, 3R, 12	Red/ Yellow				
30–100	LK4AH410CN ^[1]	4, 4X	Black				
30–100	LK4AH420CN ^[1]	4, 4X	Red/ Yellow	GS2AE2	GS2AE21	GS2AEH12	B
100–400	GS2AH130	1, 3R, 12	Black				
100–400	GS2AH140	1, 3R, 12	Red/ Yellow				
100–400	GS2AH430	4, 4X	Black	GS2AE6	GS2AE61	GS2AEH12	D
100–400	GS2AH440	4, 4X	Red/ Yellow				
600	GS2AH150	4, 4X	Black				
600	GS2AH160	4, 4X	Red/ Yellow	GS2AE6	GS2AE61	GS2AEH12	D
800–1200	GS2AH170	4, 4X	Black				
800–1200	GS2AH180	4, 4X	Red/ Yellow				

NOTE: Switches in shaded area are now available as Kits. Please see Table 8.29.

Table 8.31: Auxiliary Contacts for LK Switches

Switch Amperes	Catalog No.	Description
30–60	MDSAN11	Aux Contact 1 N.O. and 1 N.C.
30–60	MDSAN20	Aux Contact 2 N.O. and 2 N.C.
100–400	LK4AD10N	Aux Contact 1 N.O. and 1 N.C.
100–400	LK4AD20N	Aux Contact 2 N.O. and 2 N.C.
600–1200	LK4AD30N	Aux Contact Holder
600–1200	GS2AM110	Aux Contact 1 N.O.
600–1200	GS2AM101	Aux Contact 1 N.C.

[1] No longer sold as components. Purchase Kits containing Switch, Handle, Shaft, and Guide Cone as listed in Table 8.29.

[2] Components are NOT sold separately. Only 400 mm shaft can be purchase separately.

[3] Optional on shafts for LK4DU3CN, LK4GU3CN and LK4JU3CN.