

# LU2B12FU

Motor Starter Power Base (TeSys U) Reversing,  
12A, Op. Volt: 110/240V

List Price \$488.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

## Technical Characteristics

Control Connection	Screw Clamp Terminals
Power Connection	Screw Clamp Terminals
Self Protected	Yes
Ampere Rating	12A
Horsepower Rating (1-Phase)	0.5HP@115VAC - 2HP@230VAC
Horsepower Rating (3-Phase)	3HP@200/230VAC - 7.5HP@460VAC - 10HP@575/600VAC
Marketing Trade Name	TeSys
Operating Voltage	110/240 V
Weight	2.80 Pounds
Type	TeSys U
Action	Reversing
Terminal Type	Screw Clamp

## Shipping and Ordering

Category	22396 -
Discount Schedule	I11
GTIN	00785901202547
Package Quantity	1
Weight	2.95 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	FR

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.