

Copper Equipment Ground Bars

Copper equivalents of our aluminum PK-GTA equipment ground bars are available. These copper ground bars accept #14-4 Cu only.



Catalog No.
NC44SHR

Table 4.1: Copper Ground Bars for NQOD and NF Panelboards (see the Digest, Section 9 for NQ copper ground bar kits)

Maximum Number of Circuits	Maximum Ampere Rating	Catalog No.	\$ Price
12	225	8010302651	35.00
20	225	8010302652	41.00
25	225	8010302653	57.00
25	400/600	PK27GTACU	75.00

Type 1 Door-in-Door (Hinged) Trim Fronts

Features

- Meets door-in-door specifications
- Provides continuous piano hinge
- Permits one-person maintenance

Table 4.3: Hinged Trim

I-Line Fronts		NQ and NF Fronts	
Catalog No. ▲	\$ Price	Catalog No. ▲■	\$ Price
HC2652T()HR	720.00	NC26()HR	620.00
HC2665T()HR	926.00	NC32()HR	657.00
HC2674T()HR	1254.00	NC38()HR	687.00
HC2683T()HR	1557.00	NC44()HR	830.00
HC2692T()HR	1751.00	NC50()HR	912.00
HC3248T()HR	846.00	NC56()HR	983.00
HC3264T()HR	1109.00	NC62()HR	1109.00
HC3273T()HR	1514.00	NC68()HR	1185.00
HC3291T()HR	2129.00	NC74()HR	1215.00
HC4250T()HR	1298.00	NC80()HR	1245.00
HC4259T()HR	1448.00	NC86()HR	1430.00
HC4268T()HR	1841.00	NC50V()HR	912.00
HC4286T()HR	2351.00	NC56V()HR	983.00
HC4486T()HR	2351.00	NC62V()HR	1109.00
—	—	NC68V()HR	1185.00
—	—	NC74V()HR	1215.00
—	—	NC80V()HR	1245.00
—	—	NC86V()HR	1430.00

- ▲ Add "S" for surface or "F" for flush in place of the parentheses.
- For welded metal directory, add "WMD" suffix to the end of the catalog number and add \$75.00 to the price.

Field Installable I-Line® Door Kits

Table 4.2: I-Line Door Kits

Panel Type	Catalog No. ▲	\$ Price
HCN	HCN52D()	77.00
	HCN65D()	90.00
	HCN74D()	122.00
	HCN83D()	137.00
	HCN92D()	155.00
HCM	HCM48D()	227.00
	HCM64D()	254.00
	HCM73D()	333.00
	HCM91D()	390.00
HCP	HCW50D	323.00
	HCW59D	351.00
	HCW68D	422.00
	HCW86D	467.00
HCRU	HCW86D	467.00

- ▲ Add "S" for surface or "F" for flush in place of the parentheses.