



Schneider Electric USA
1415 South Roselle Road
Palatine, IL 60067
Customer Care Center: 1-888-778-2733
Web: www.schneider-electric.us

ALL CATEGORIES > CIRCUIT BREAKERS - MICROLOGIC ELECTRONIC TRIP > MOLDED CASE CIRCUIT BREAKERS
- POWERPACT P-FRAME > UNIT MOUNT - 3 POLE MANUALLY OPERATED MOLDED CASE CIRCUIT BREAKER W/
LUGS > ITEM # PJL36100U43A

ITEM # PJL36100U43A, INTERRUPTING RATING 65KA AT 240VAC - 35KA AT 480VAC - 18KA AT 600VAC

PowerPact P-frame Electronic Trip Circuit Breaker



Specifications

Sensor Rating	1000A
General Application	Provides overload and short circuit protection
Approvals	UL Listed - CSA Certified - IEC Rated
For Use With	Panelboards and Switchboards
Installed Rating Plug	Type A
Voltage Rating	600VAC
Electronic Trip Unit	Micrologic Ammeter Trip Unit (5.0A)
Mounting Type	Unit Mount
Weight	32 Pounds
Number of Poles	3-Pole
Rating Plug Range	0.4A to 1A

Interrupting Rating	100kA at 240VAC - 65kA at 480VAC - 25kA at 600VAC
Circuit Breaker Rating	80% Rated
Terminal Type	Lugs (ON and OFF ends)
Trip Function	LSI
Wire Size	#3/0-500 AWG/kcmil(Al/Cu)
Depth	8.07 Inches
Height	16.26 Inches
Width	8.27 Inches