



Main

Commercial Status	Commercialised
Range of product	Zelio Time
Product or component type	Optimum industrial timing relay
Component name	RE8
Time delay type	A
Time delay range	0.1...10 s
[Us] rated supply voltage	24 V AC/DC, 50/60 Hz 110...240 V AC, 50/60 Hz
Sale per indivisible quantity	1

Complementary

Discrete output type	Relay
Contacts material	Silver nickel contacts
Width pitch dimension	0.89 in (22.5 mm)
Voltage range	0.9...1.1 Us
Connections - terminals	Screw terminals 2 x 2.5 mm ² , flexible cable without cable end Screw terminals 2 x 1.5 mm ² , flexible cable with cable end
Tightening torque	5.31...9.73 lbf.in (0.6...1.1 N.m)
Setting accuracy of time delay	+/- 20 % of full scale
Repeat accuracy	< 1 %
Voltage drift	< 2.5 %/V
Temperature drift	< 0.2 %/°C
Minimum pulse duration	26 ms
Reset time	50 ms
Maximum switching voltage	250 V
Mechanical durability	20000000 cycles
[Ith] conventional free air thermal current	8 A
[Ie] rated operational current	<= 0.2 A at 115 V, DC-13 for 158 °F (70 °C) conforming to VDE 0660 <= 0.2 A at 115 V, DC-13 for 158 °F (70 °C) conforming to IEC 60947-5-1/1991 <= 0.1 A at 250 V, DC-13 for 158 °F (70 °C) conforming to VDE 0660 <= 0.1 A at 250 V, DC-13 for 158 °F (70 °C) conforming to IEC 60947-5-1/1991 <= 3 A at 24 V, AC-15 for 158 °F (70 °C) conforming to VDE 0660 <= 3 A at 24 V, AC-15 for 158 °F (70 °C) conforming to IEC 60947-5-1/1991 <= 2 A at 24 V, DC-13 for 158 °F (70 °C) conforming to VDE 0660 <= 2 A at 24 V, DC-13 for 158 °F (70 °C) conforming to IEC 60947-5-1/1991
Minimum switching capacity	10 mA at 12 V
Marking	CE
Overvoltage category	III conforming to IEC 60664-1
[Ui] rated insulation voltage	300 V conforming to CSA 250 V conforming to IEC
Supply disconnection value	> 0.1 Uc
Operating position	Any position without derating factor
Surge withstand	2 kV conforming to IEC 61000-4-5 level 3
Power consumption in VA	8.5 VA at 240 V 1.8 VA at 110 V 0.7 VA at 24 V
Power consumption in W	0.5 W at 24 V
Terminal description	(15-16-18)OC_OFF (A1-B1)CO ALT

Height	3.07 in (78 mm)
Width	0.89 in (22.5 mm)
Depth	3.15 in (80 mm)
Product weight	0.24 lb(US) (0.11 kg)

Environment

Immunity to microbreaks	3 ms
Standards	EN/IEC 61812-1
Product certifications	CSA GL UL
Ambient air temperature for storage	-40...185 °F (-40...85 °C)
Ambient air temperature for operation	-4...140 °F (-20...60 °C)
Relative humidity	15...85 % 3K3 conforming to IEC 60721-3-3
Vibration resistance	0.35 mm 10...55 Hz conforming to IEC 60068-2-6
Shock resistance	15 gn (duration = 11 ms conforming to IEC 60068-2-27)
IP degree of protection	IP50 (casing) IP20 (terminals)
Pollution degree	3 conforming to IEC 60664-1
Dielectric test voltage	2.5 kV
Non-dissipating shock wave	4.8 kV
Resistance to electrostatic discharge	8 kV in air conforming to IEC 61000-4-2 level 3 6 kV in contact conforming to IEC 61000-4-2 level 3
Resistance to electromagnetic fields	9.14 V/yd (10 V/m) conforming to IEC 61000-4-3 level 3
Resistance to fast transients	2 kV conforming to IEC 61000-4-4 level 3
Disturbance radiated/conducted	CISPR 11 group 1 - class A CISPR 22 - class A

Ordering and shipping details

Category	22376 - RELAYS-MEASUREMENT(RM4)
Discount Schedule	CP2
GTIN	00785901471134
Nbr. of units in pkg.	1
Package weight(Lbs)	0.24
Product availability	Non-Stock - Not normally stocked in distribution facility
Returnability	N
Country of origin	ID

Contractual warranty

Period	18 months
--------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[RE8TA11BU](#)