



RUMC21BD



RUMF21F7



RUMC32BD



RUMF32F7



RUMF33P7

References						
Pins	Control circuit voltage	Number and type of contacts - Thermal current (Ith)				
		2 C/O - 10 A		3 C/O - 10 A		
		Unit reference	Weight	Unit reference	Weight	
			kg/lb		kg/lb	
Universal relays with lockable test button only (sold in lots of 10)						
Cylindrical	12 Vdc	RUMC21JD	0.086/0.190	RUMC31JD	0.086/0.190	
	24 Vdc	RUMC21BD	0.086/0.190	RUMC31BD	0.086/0.190	
	48 Vdc	RUMC21ED	0.086/0.190	RUMC31ED	0.086/0.190	
	60 Vdc	–	–	RUMC31ND	0.086/0.190	
	110 Vdc	RUMC21FD	0.086/0.190	RUMC31FD	0.086/0.190	
	125 Vdc	–	–	RUMC31GD	0.086/0.190	
	220 Vdc	–	–	RUMC31MD	0.086/0.190	
	24 Vac	RUMC21B7	0.086/0.190	RUMC31B7	0.086/0.190	
	48 Vac	RUMC21E7	0.086/0.190	RUMC31E7	0.086/0.190	
	120 Vac	RUMC21F7	0.086/0.190	RUMC31F7	0.086/0.190	
	230 Vac	RUMC21P7	0.086/0.190	RUMC31P7	0.086/0.190	
	Flat (Faston type)	12 Vdc	RUMF21JD	0.086/0.190	RUMF31JD	0.086/0.190
		24 Vdc	RUMF21BD	0.086/0.190	RUMF31BD	0.086/0.190
48 Vdc		RUMF21ED	0.086/0.190	RUMF31ED	0.086/0.190	
110 Vdc		RUMF21FD	0.086/0.190	RUMF31FD	0.086/0.190	
24 Vac		RUMF21B7	0.086/0.190	RUMF31B7	0.086/0.190	
48 Vac		RUMF21E7	0.086/0.190	RUMF31E7	0.086/0.190	
120 Vac		RUMF21F7	0.086/0.190	RUMF31F7	0.086/0.190	
230 Vac		RUMF21P7	0.086/0.190	RUMF31P7	0.086/0.190	
Universal relays with lockable test button and LED (sold in lots of 10)						
Cylindrical		12 Vdc	RUMC22JD	0.086/0.190	RUMC32JD	0.086/0.190
		24 Vdc	RUMC22BD	0.086/0.190	RUMC32BD	0.086/0.190
		48 Vdc	RUMC22ED	0.086/0.190	RUMC32ED	0.086/0.190
		60 Vdc	–	–	RUMC32ND	0.086/0.190
	110 Vdc	RUMC22FD	0.086/0.190	RUMC32FD	0.086/0.190	
	125 Vdc	–	–	RUMC32GD	0.086/0.190	
	24 Vac	RUMC22B7	0.086/0.190	RUMC32B7	0.086/0.190	
	48 Vac	RUMC22E7	0.086/0.190	RUMC32E7	0.086/0.190	
	120 Vac	RUMC22F7	0.086/0.190	RUMC32F7	0.086/0.190	
	230 Vac	RUMC22P7	0.086/0.190	RUMC32P7	0.086/0.190	
	Flat (Faston type)	12 Vdc	RUMF22JD	0.086/0.190	RUMF32JD	0.086/0.190
		24 Vdc	RUMF22BD	0.086/0.190	RUMF32BD	0.086/0.190
		48 Vdc	RUMF22ED	0.086/0.190	RUMF32ED	0.086/0.190
110 Vdc		RUMF22FD	0.086/0.190	RUMF32FD	0.086/0.190	
24 Vac		RUMF22B7	0.086/0.190	RUMF32B7	0.086/0.190	
48 Vac		RUMF22E7	0.086/0.190	RUMF32E7	0.086/0.190	
120 Vac		RUMF22F7	0.086/0.190	RUMF32F7	0.086/0.190	
230 Vac		RUMF22P7	0.086/0.190	RUMF32P7	0.086/0.190	
Universal relays with LED only (sold in lots of 10)						
Cylindrical pins		12 Vdc	RUMC23JD	0.086/0.190	RUMC33JD	0.086/0.190
		24 Vdc	RUMC23BD	0.086/0.190	RUMC33BD	0.086/0.190
		48 Vdc	RUMC23ED	0.086/0.190	RUMC33ED	0.086/0.190
		60 Vdc	–	–	RUMC33ND	0.086/0.190
	110 Vdc	RUMC23FD	0.086/0.190	RUMC33FD	0.086/0.190	
	125 Vdc	–	–	RUMC33GD	0.086/0.190	
	24 Vac	RUMC23B7	0.086/0.190	RUMC33B7	0.086/0.190	
	48 Vac	RUMC23E7	0.086/0.190	RUMC33E7	0.086/0.190	
	120 Vac	RUMC23F7	0.086/0.190	RUMC33F7	0.086/0.190	
	230 Vac	RUMC23P7	0.086/0.190	RUMC33P7	0.086/0.190	
	Quick-connect pins	12 Vdc	RUMF23JD	0.086/0.190	RUMF33JD	0.086/0.190
		24 Vdc	RUMF23BD	0.086/0.190	RUMF33BD	0.086/0.190
		48 Vdc	RUMF23ED	0.086/0.190	RUMF33ED	0.086/0.190
110 Vdc		RUMF23FD	0.086/0.190	RUMF33FD	0.086/0.190	
24 Vac		RUMF23B7	0.086/0.190	RUMF33B7	0.086/0.190	
48 Vac		RUMF23E7	0.086/0.190	RUMF33E7	0.086/0.190	
120 Vac		RUMF23F7	0.086/0.190	RUMF33F7	0.086/0.190	
230 Vac		RUMF23P7	0.086/0.190	RUMF33P7	0.086/0.190	