



Technical Characteristics

Application	Suitable for use in service entrance locations
Approvals	Listed to UL 1449 Second Edition and UL 1283 - Meets requirements of ANSI/IEEE C62.41 and C62.45 and UL Category Section 37.3
Wiring Configuration	3 or 4-Wire
LED Indicator	Normal: Green - Fault: Red (for each phase)
Marketing Trade Name	SurgeLogic
Short Circuit Current Rating	200kA
Maximum Surge Current	120kA/phase
Enclosure Rating	NEMA 3R/12
Catalog Reference Number	1310CT0202
Enclosure Material	Painted Steel
Includes	Surge Counter and Audible alarm (with enable/disable switch)
Mounting Type	Surface/Flush
Phase	3-Phase
Service Voltage	208Y/120VAC
Type	EMA

Shipping and Ordering

Category	08252 - Panelboards,
Discount Schedule	PE1A
Article Number	785901633440
Package Quantity	1
Weight	22.2 lbs.
Availability Code	Non-Stock Item: This item is not normally stocked in our distribution facility.
Returnability	Y

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.