

List Price \$190.00 USD

Availability **Factory Item: This item is stocked at a Schneider Electric manufacturing plant.****Technical Characteristics**

Ampere Rating	10A
Unlock Method	Not Lockable
Contact Configuration	2 N.O./1 N.C.
Maximum Voltage Rating	300VAC
Type	XCSA
Width	1.57 Inches
Terminal Type	Screw Clamp
Wire Size	#14 to #20 AWG
Actuator Type	Key
Lock Method	Not Lockable
Approvals	UL Listed File Number: E164353 CCN NKCR - CSA Certified File Number: LR4408794 Class 3211 03 - CE Marked
Catalog Reference Number	9007CT0201
Depth	1.73 Inches
Connection Type	(1) 0.5 Inch NPT (Conduit Entrance)
Contact Operation	Slow Break (Break before Make)
Enclosure Rating	NEMA 4/4X/12 - IP67
Enclosure Material	Metal
Enclosure Type	Water tight, Dust tight and Corrosion resistant (Indoor/Outdoor)
Operating Temperature Range	-13 to 158 Degrees F
Weight	15.5 Ounces
Number of Poles	3-Pole
Height	4.47 Inches
Orientation	Actuating Key: Field Selectable - Electromagnet: Via conduit entrance

Shipping and Ordering

Category	22411 - Limit Switches, Heavy Duty, IEC, Type XCKJ
Discount Schedule	T
Article Number	785901718871
Package Quantity	1
Weight	1.11 lbs.
Availability Code	Factory Item: This item is stocked at a Schneider Electric manufacturing plant.
Returnability	Y

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.