

Product data sheet

Characteristics

QO215CAF1

QO Miniature Circuit Breaker 15A 2P 120/240V 10kA Plug-in Mount

Product availability : Stock - Normally stocked in distribution facility



Price* : 636.00 USD



Main

| | |
|-----------------------------|---------------------------|
| Product or component type | Miniature circuit-breaker |
| Range of product | QO |
| Line Rated Current | 15 A |
| System Voltage | 120/240 V AC |
| Mounting mode | Plug-in |
| Poles description | 2P |
| Circuit breaker type | Combination ARC-fault |
| Circuit breaker application | Not rated |
| Electrical connection | Pressure plate |

Complementary

| | |
|---------------------------|---|
| Breaking capacity | 10 kA at: 120/240 V AC |
| Number of spaces required | 2 |
| AWG gauge | AWG 14...AWG 8 (copper) AWG 12...AWG 8 (aluminium) |
| Height | 4.75 in |
| Depth | 2.91 in |
| Width | 1.5 in |

Environment

| | |
|---------------------------------------|------------------|
| Product certifications | CSA UL listed |
| Ambient air temperature for operation | 104 °F (40 °C) |

Ordering and shipping details

| | |
|----------|--|
| Category | 06303 - QO SINGLE POLE ARC FAULT CIRCUIT BREAKER |
|----------|--|

| | |
|-----------------------|--------------------|
| Discount Schedule | DE2A |
| GTIN | 00785901388517 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.9500000000000007 |
| Returnability | Y |
| Country of origin | MX |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 1344 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference contains SVHC above the threshold - Go to CaP for more details Go to CaP for more details |
| Product environmental profile | Available |
| Product end of life instructions | Available |