



Job Name:

Job Type:

Comments:

Quantity:

9784: 20W Halogen Bi-Pin Clear Bulb

Dimensions:

Diameter: 3/8"
Length: 13/16"

Bulb Appearance: Clear
Gas Filled: Halogen
Volts: 12
Watts: 20
Watts Consumed: 20
Watts Rated: 20
Hours Rated: 1500
Lumens: 320
Bulb Temp: 2900 °K



Features:

- Clear bulb(s) recommended for this fixture

Material List:

1 Bulb - Glass - Clear

Safety Listing:

Not Listed Listed

Collection: Ambiance Mini-recessed Lamp Sources

20W Halogen T3, G4 Bi-Pin Base Clear Bulb

T3 G4 Bi-Pin Halogen

UPC #:785652978401

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	9784	1	785652978401	2	1	1	0.001	0.01	Yes
Master Pack		50	10785652978408	4.5	2.25	2	0.012	5	Yes
NJ Pallet		32000		45	40	50	52.083	320	No
NV Pallet		32000		45	40	50	52.083	320	No