



9793: 35w 12V T3 G4 Bi-Pin Halogen Lamp

Dimensions:

Diameter: 1/2"
Length: 1 1/8"

Bulb Appearance: Clear - Glass Lens

Gas Filled: Halogen

Bulb Type: T3

Bulb Base: G4 Bi-Pin

Volts: 12

Watts: 35

Watts Consumed: 35

Watts Rated: 35

Hours Rated: 2000

Lumens: 650

Bulb Temp: 2800 °K

CRI: 90

35W Halogen T4, GY6.35 Bi-Pin Base Clear Bulb

35W Halogen T4, GY6.35 Bi-Pin Base Clear Bulb

UPC #:785652979309

Features:

- Clear bulb(s) recommended for this fixture

Material List:

1 Bulb - Glass - Clear

Instruction Sheets:

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	9793	1	785652979309	0.9	2.6	0.9	0.001	0.02	60	Yes
Master Pack		10	10785652979306	3	4.6	2	0.016	0.2	60	Yes
NJ Pallet		5000		48	40	65	72.222	84		No
NV Pallet		5000		48	40	65	72.222	84		No