



Job Name:

Job Type:

Comments:

Quantity:

98061-12: 100W 12V direct wire zero load electronic transformer, black finish

Dimensions:

Length: 7 15/16"

Width: 2"

Height: 1"

Material List:

Safety Listing:

ETL Listed for Dry Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (HC-1844FS)



Collections: Ambiance® Lx Lite - Flexible LED Tape (Primary)
Ambiance Lx Lite Transformer
Ambiance® LED Under Cabinet

UL 2108, hardwire 100w 12v Zero-Load electronic transformer in Black Finish. With terminal blocks for permanent in-line wiring. For use with 12VAC Pure LED, LED flexible strip lighting. 10 ft. output cord attached directly to LED tape.

UL 2108 approved, flame resistant plastic cases with wiring compartment & integrated strain relief (input side).

Low profile design that mounts neatly out of view (1"H x 1.6"W x 5"L)

Compatible with most standard dimmers including electronic low voltage dimmers (recommended)

Electronic circuit design for increased efficiency & reliability

Short circuit & overload protection, automatic shut down/reset

Emits no audible noise, sound rated A

Maximum operating temperatures -20°C to +90°C

Input 120VAC, output 12VAC 0-100W

High power factor > 95%

ETL listed, dry location

New/improved transformer case/enclosure: An electrically isolated, flame resistant, UL 2108 approved plastic enclosure

UPC #:785652159428

Finish: Black (12)

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	98061-12	1	785652159428	9	4	4	0.083	0.8	Yes
Master Pack	98061-12	6	10785652159425	18.25	8.5	5.25	0.471	5.6	Yes