



Job Name:

Job Type:

Comments:

Quantity:

**98062-12: 100W 24V direct wire zero load electronic transformer, black finish**

**Dimensions:**

**Length:** 7"  
**Width:** 2"  
**Height:** 1"

**Material List:**

**Safety Listing:**

ETL Listed for Dry Locations

**Instruction Sheets:**

Trilingual (English, Spanish, and French) (HC-1844FS)



**Collections:** Ambiance Lx Lite Transformer (Primary)  
Ambiance® LED Under Cabinet  
Ambiance® Lx Lite - Flexible LED Tape

UL 2108, hardwire 100w 24v Zero-Load electronic transformer in Black Finish. With terminal blocks for permanent in-line wiring. For use with 24V Pure LED, LED flexible strip lighting.

UL 2108 approved, flame resistant plastic cases with wiring compartment & integrated strain relief (input side).

Low profile design that mounts neatly out of view (1"H x 1.6"W x 5"L)

Compatible with most standard dimmers including electronic low voltage dimmers (recommended)

Electronic circuit design for increased efficiency & reliability

Short circuit & overload protection, automatic shut down/reset

Emits no audible noise, sound rated A

Maximum operating temperatures -20°C to +90°C

Input 120VAC, output 24VAC 0-100W

High power factor > 95%

ETL listed, dry location

New/improved transformer case/enclosure: An electrically isolated, flame resistant, UL 2108 approved plastic enclosure

**UPC #:785652183348**

**Finish:** Black (12)

### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	98062-12	1	785652183348	9	4	4	0.083	0.9	Yes
Master Pack	98062-12	6	10785652183345	18.25	8.5	5.25	0.471	5.8	Yes