



Job Name:

Job Type:

Comments:

Quantity:

98611SW-15: 24V LED strip lighting, 2 inch section, white face, 3000K 85 CRI

Dimensions:

Length: 2"
Width: 3/8"
Height: 1/8"

Mounting Proc.: Dual Mount



Features:

- The advanced LED technology in Sea Gull Lighting products is carefully designed and selected to consist of the highest quality LED chipsets for superior performance and reliability.

Material List:

Safety Listing:

cETL Listed for Damp Locations



Collections: Ambiance® Lx Lite - Flexible LED Tape (Primary)
Ambiance® LED Under Cabinet

2 inch section of 24V Ambiance Lx Lite, Flexible LED Tape lighting with white PCB face. Connects to other sections of 24V LED Tape lighting. Sea Gull's Ambiance Lx Lite, Flexible LED Tape lighting contains 12 warm white LEDs per foot on flexible copper strip encased in optically clear protective coating. Lx Lite Tape lighting works and dims with all 24VAC magnetic transformers. For increased light output LED Tape lighting can also be powered by 24 VDC LED power supply unit. Installs easily on surfaces with included clips or self adhering industrial 3M adhesive (provided on back of strip). Maximum run length for 24V is 40 feet.

Available in a variety of lengths including 1ft, 5ft, 16ft and 2 inch sections and with wide variety of connectors. Field cuttable at every inches to end a run

provides the look and feel of halogen and xenon with energy savings of up to 90%

12 LEDs per foot produces 150 lumens per foot and consumes 3 watts 12VAC per foot. Power using VDC for increased light output of 180 lumens per foot. 2 in. section of LED tape consumes .4 watts.

Lumen package is comparable to traditional undercabinet lighting 10W xenon to 20W halogen 4 inch to 6 inch on center

Long 40,000 hour life last 20X's longer than halogen for maintenance free operation

Color accurate illumination CRI 85, 3000K CCT- improves visibility and perceived brightness

24VAC or 24VDC operation, dimmable with a wide range of incandescent and ELV dimmers, can be connected to 24VAC Ambiance LX systems

CETL listed, damp location

Environmentally friendly, contains no mercury and emits no UV or IR

UPC #:785652158650

Finish: White (15)

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	98611SW-15	1	785652158650	3	1.75	0.75	0.002	0.1	Yes
Master Pack	98611SW-15	24	10785652158657	7.25	4.5	3.25	0.061	0.8	Yes