



Job Name:

Job Type:

Comments:

Quantity:

**98640S-12: Plug-in, 12VAC 30/w Zero Load Electronic Transformer, black finish**

**Dimensions:**



**Length:** 3 5/16"

**Wire:** 96" (color/Black)

**Width:** 1 1/2"

**Switch Type:** On/Off Switch

**Height:** 1 1/4"

**Connection:** Plug Into Box

**Features:**

- The advanced LED technology in Sea Gull Lighting products is carefully designed and selected to consist of the highest quality LED chipsets for superior performance and reliability.

**Material List:**

**Safety Listing:**

cETL Listed for Damp Locations

**Collections:** Ambiance® LED Disk Lighting (Primary)  
Ambiance® LED Under Cabinet

12VAC, 30W zero-Load electronic transformer in back finish with integral on / off switch and 8' output cord for connection of LED disk or mounting hub for LED disks

No minimum load, Input 120VAC, Output 12VAC 0-30W output

Electronic circuit design for increased efficiency & reliability

Short circuit & overload protection, automatic shut down/reset

Emits no audible noise, sound rated A

Maximum operating temperatures -20°C to +90°C

Electrically isolated, flame resistant, UL 2108 approved plastic enclosure

ETL listed, damp location

**UPC #:**785652153235

**Finish:** Black (12)

**Shipping Information:**

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	98640S-12	1	785652153235	4.75	2	2.625	0.014	0.3	Yes
Master Pack	98640S-12	3	10785652153232	5.75	5.375	3.125	0.056	0.9	Yes
Shipping Master		30	20785652153239	15.625	11	7.125	0.709	9.8	Yes