



Job Name:

Job Type:

Comments:

Quantity:

98683SW-15: 24V LED Tape Lighting, 5 foot section, 2700K



Dimensions:

Length:	60"
Width:	3/8"
Height:	1/8"

Features:

- The advanced LED technology in Sea Gull Lighting products is carefully designed and selected to consist of the highest quality LED chipsets for superior performance and reliability.

Material List:

Safety Listing:

cETL Listed for Damp Locations

Collections: Ambiance® Lx Lite - Flexible LED Tape (Primary)
Ambiance® LED Under Cabinet

5 foot section of 24V Lx Lite Flexible LED Tape Lighting with white PCB face. Male and female ends to connect to other sections of 24V LED tape lighting. Sea Gull's Lx Lite, LED Tape Lighting contains 12 warm white LEDs per foot on flexible copper strip encased in optically clear protective coating. Lx Lite Tape Lighting works and dims with all 24VAC magnetic transformers. For increased light output Lx Lite LED Tape Lighting can also be powered by 24VDC LED power supply units. Installs easily on surfaces with clips or self adhering industrial 3M adhesive (provided on back of strip). Maximum run length for 24V is 40 feet.

Versatile LED linear lighting, ultra low profile 1/8" H x 3/8" W - easily fits into any space. Flexible - bend lengthwise or curve laterally.

Available in a variety of lengths including 1ft, 5ft, 16ft and 2 inch sections and with wide variety of connectors. Field cuttable at every 2 inches to end a run

The look and feel of halogen and xenon while reducing energy and operating costs by up to 90%

12 LEDs per foot produce 180 - 200 lumens per foot and consume 3 watts per foot

Lumen package is comparable to traditional undercabinet lighting
10W xenon to 20W halogen 4 to 6 inches on center

Long 40,000 hour life last 20X's longer than halogen for maintenance free operation

Color accurate illumination CRI 85, 2700K color- improves visibility and perceived brightness

24VAC or 24VDC operation, dimmable with a wide range of incandescent and ELV dimmers, can be connected to 24VAC Ambiance systems

CETL listed, damp location

UPC #:785652212116

Finish: White (15)

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	98683SW-15	1	785652212116	10	9.25	0.75	0.04	0.4	Yes
Master Pack	98683SW-15	5	10785652212113	10.25	9.75	4.75	0.275	2.3	Yes