



Job Name:

Job Type:

Comments:

Quantity:

98862SW-12: 2 LED Disk Light Kit, Black Finish



Dimensions:

Diameter: 3"

Wire: 96" (color/Black)

Height: 5/8"

Mounting Proc.: Dual Mount

Connection: Plug Into Box

Features:

- The advanced LED technology in Sea Gull Lighting products is carefully designed and selected to consist of the highest quality LED chipsets for superior performance and reliability.

Material List:

Safety Listing:

cETL Listed for Damp Locations

Instruction Sheets:

English (HC-1887FS)

Trilingual (English, Spanish, and French) (HC-1887FS)

Collections: Ambiance® LED Disk Lighting (Primary)
Ambiance® LED Under Cabinet

2 LED Disk Light Kit in black finish. Kit includes mounting hub and plug in 12VAC 30W zero load electronic transformer with 96" output cord

Performance 170 lumens, 4 watts per disk, power supply consumes 1-1.5 watts (12VAC)

The look, feel and performance of halogen/xenon disks while reducing energy and operating cost by up to 80%

Delivers light output of 170 lumens using only 4 watts per watt per puck. Total light: 340 lumens per kit

Each LED Disk contains 3 integrated multi-LED Nichia LED chip packages

Long 40,000 hours life - last 20X's longer than halogen for maintenance free operation

Includes black, plug-in 12VAC 30W, zero load, electronic transformer with built in on/off switch and 8' output cord connects directly to pucks or mounting hub

Configurable and linkable for easier multiple unit installations. Daisy chain up to 6 disks from one to another or hub and spoke mount with included mounting hub

Color accurate illumination 85CRI, 3000K

Low profile, aluminum housing for cooler operation and maximum LED life

Available in 3 painted finishes; white, black, bronze and (plated) tinted aluminum

Surface or recessed mounting

Each disk includes 36" lead wire for connection to additional LED disk
or included mounting hub

UPC #:785652153150

Finish: Black (12)

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	98862SW-12	1	785652153150	4	4.25	5	0.049	0.9	Yes
Master Pack	98862SW-12	3	10785652153157	16	5	5.25	0.243	3.1	Yes
Shipping Master		30							