



**59270LE-15: Two Light Ceiling Flush Mount**



**Dimensions:**

**Length:** 51 1/2"      **Wire:** 6 1/2"  
**Width:** 11 1/4"      **Connection:** Mounted To Box  
**Height:** 5 3/4"

**Bulbs:**

2 - Fluorescent Medium Bi-Pin T8 32w Max. 120v - Not included

**Features:**

- Offers energy saving fluorescent lighting
- Meets Title 24 energy efficiency standards
- Title 24 compliant high efficacy light source that is not required to be listed in the California Energy Commission Appliance database.

**Material List:**

1 Body - Steel - White

**Safety Listing:**

Safety Listed for Damp Locations

**Instruction Sheets:**

English (HC-1297)  
 English (A-779)

**Collection:** Fluorescent Ceiling

Fluorescent Two Light Cloud in White Finish with White Acrylic Diffuser

**UPC #:**785652592720

**Finish:** White (15)

**Shade / Glass / Diffuser Details:**

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Diffuser	Acrylic	White	1									

**Shipping Information:**

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	59270LE-15	1	785652592720	54	12	7.5	2.813	12.7	150	Yes
NJ Pallet		29		55	44	65.25	91.38	368.3		No
NV Pallet		30		55	40	79	100.579	381		No