



### 89250BLE-12: One Light Outdoor Wall Lantern



#### Dimensions:

**Width:** 10"      **Extends:** 12"  
**Height:** 16 1/4"      **Wire:** 6 1/2"  
**Mounting Proc.:** Cap Nuts  
**Connection:** Mounted To Box

#### Bulbs:

1 - Fluorescent GU24 Self Ballasted CFL 18w Max. 120v - included

#### Features:

- ENERGY STAR® Qualified
- Offers energy saving fluorescent lighting
- Meets Title 24 energy efficiency standards

#### Material List:

1 Body - Die Cast Aluminum - Undefined

#### Safety Listing:

Safety Listed for Wet Locations  
 Safety Listed for Wet Locations

#### Instruction Sheets:

French (F-009)  
 Bilingual (English - French) (HC-640)

**Collection:** Yorktown

One Light Outdoor Wall Fixture in Black Finish with Swirled Marbleized Glass

This replaces 89050BL-12

**UPC #:**785652199028

**Finish:** Black (12)

#### Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Panel	Glass	Swirled Marbleize	4									

#### Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	9	5 1/2	1		9	7 1/4

#### Replacement Bulb Data:

Product #	Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97107	Frosted Glass Lens	GU24	18	18	120v	10000	1100	2700	82

#### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	89250BLE-12	1	785652199028	14.25	12	9.25	0.915	7.4	100	Yes
NJ Pallet		36		48	40	72	80	266.4		No
NV Pallet		36		48	40	72	80	266.4		No