



Job Name:

Job Type:

Comments:

Quantity:

39059BLE-962: Five Light Chandelier**Dimensions:**

Diameter: 29"
Height: 22 1/2"

Overall Height: 59"**Wire:** 144" (color/Clear)**Chain:** 36"**Mounting Proc.:** Center Lock-Up**Connection:** Mounted To Box**Bulbs:**

5 - Fluorescent GU24 Self Ballasted CFL 13w Max. 120v - included

Features:

- ENERGY STAR® Qualified
- Offers energy saving fluorescent lighting
- Meets Title 24 energy efficiency standards

Material List:

1 Body - Steel - Brushed Nickel
 1 Chain - Steel - Brushed Nickel

Safety Listing:

Safety Listed for Dry Locations
 Safety Listed for Dry Locations

Instruction Sheets:

English (HC-830)
 French (F-004)

Collection: Serenity

Five Light Fluorescent Chandelier in Brushed Nickel Finish with Excavated Alabaster Glass Shades. Energy Star Compliant Bulb Included.

A soft, contemporary design in brushed nickel finish with excavated alabaster glass. A fluorescent Energy Star Compliant fixture.

Design#: D20112

UPC #:785652390524

Finish: Brushed Nickel (962)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Excavated Alabaster	5					8 1/2				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy			1 1/4	5 1/2		

Replacement Bulb Data:

Product #		Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97102	Frosted Glass Lens	Self Ballasted CFL	GU24	13	13	120v	10000	900	2700	81

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	39059BLE-962	1	785652390524	26.75	13	20	4.025	21.2	150	Yes
NJ Pallet		18		48	40	68.5	76.111	381.6		No
NV Pallet		18		48	40	68.5	76.111	381.6		No