

Products

Indoor Lighting

- Chandeliers
- Wall / Bath Lighting
- Wall Sconces
- Pendant Lighting
- Mini-Pendants
- Ceiling Lighting
- Recessed Lighting
- Under Cabinet Lights
- Track Lighting
- Rail Lighting
- Foyer Lighting
- Fluorescent Lighting
- LED Lighting

Outdoor Lighting

- Outdoor Wall Lanterns
- Outdoor Pendants
- Outdoor Ceiling Lighting
- Outdoor Ceiling Fans
- Outdoor Spot Lights
- Outdoor Post Lanterns
- House Signs
- Outdoor Fluorescent
- Outdoor ENERGY STAR®
- Outdoor Accessories
- Dark Sky
- Ambiance Landscape
- Unique Landscape

Lighting

- Outdoor LED Lighting

Ceiling Fans

- Indoor Ceiling Fans
- Outdoor Ceiling Fans
- Ceiling Fan Light Kits
- Ceiling Fan Glass
- Ceiling Fan Accessories
- Energy Star Fans

ENERGY STAR®

- Chandeliers
- Bath Lighting
- Wall Sconces
- Pendant Lighting
- Ceiling Lighting
- Foyer Lighting
- Ceiling Fans
- Recessed Lighting
- Outdoor Lighting
- Calculate Your Savings

Ambiance®

- Flexible LED Tape
- Low Voltage Linear
- Low Voltage Rail Lighting
- 120v Rail Lighting
- Low Voltage Disk Lighting
- Low Voltage Recessed
- LED Lighting
- Landscape Lighting
- Xenon & Halogen Bulbs
- Glass & Shades

Transitions

- Urban Loft
- Torry

White Miniature Recessed Light



Alternate Images (click below for detail view)



Catalog Views: 2012 Full Line Catalog
2009 Ambiance Lighting Catalog
Recessed - March 2009

Description

Transformer not included. UV stablized silicone transformer. UV stablized silicone rubber flood trim with glass lens. Trim rotates 360°, center beam fixed at 30° from center. MR 11 lamps maximize light output and offer height intensity, crisp, white light. Choose lamps with various beams to suit any application.

Wattage: One MR11 20w max.

Suitable for shower use.

Ambiance Miniature Recessed Lighting Die Cast Aluminum Housing

Specifications

- Product #: 9424-15
- MSRP: \$55.20
- Finish: White
- Diffuser: Glass - Clear Tempered
- Dimensions: D: 2 3/4" H: 3 1/4"
- Listings: UL Listed for Dry Locations
cUL Listed for Dry Locations
cETL Listed for Locations

Warranty: 1-Year Warranty

- Wish List
- Compare

Details

- **FIXTURES INCLUDE:**
- Non-IC remodel miniature die-cast aluminum housing with powdercoat finish.
- Built in wiring compartment allows easy installation of romex or BX feed cable. One in 12/2 or one in, one out 14/2.
- Built-in thermal protector safeguards against overheating.
- For use with remote transformer.
- Adjustable flange clips for east installation into .375" to 1.5" thick material.
- Well suited for commercial and residential applications.
- Adjustable socket accommodates a variety of decorative trims and lamps.
- Listed for damp locations 12v.
- Overall Height: 4 1/4"
- Powdercoat finish included long finish life

Detailed Specs:

[HTML Specification Sheet](#)

[PDF Specification Sheet](#)

Other Finishes:

Black

How to Install:

English

HI-RES Downloads

- [.jpg](#)
- [.png](#)

Need Parts?

Diffuser: 5101-610

Rustica
Saratoga
Trenton
Sconces
Pendants
Directionals
Glass
Transitions Bulbs
Accessories

[About Us](#)

[Warranty](#)

[Press Releases](#)

[Application Images](#)

[Collections](#)

[Our Brands](#)

[Lighting Finder](#)

[Text Catalog](#)

© 2012 Sea Gull Lighting Products, LLC a Generation Brands Company