

Keyword/Model Search  
[home](#) ▶

- Product Specials
- Clamp-On Meters
- Multimeters
- Wire Tracers
- Megohmmeters
- Ground Resistance
- Power Quality
- Environmental Testers
- Electrical Testers
- Phase Sequence
- Component Test
- Relays
- Benchtop Instruments
- Accessories
- Replacement Parts

## Model: CT-100 Wire Tracer

[Home](#)
[Features](#) | [Specs](#) | [Accessories](#) | [Parts](#)


- Heavy duty, recommended for tough industrial applications
- Traces live wires buried underground or hidden behind walls up to 4 feet deep
- Performs tests without having to interrupt power
- Locates breakers, neutral and ground lines
- Locates and traces wires in walls, floors, conduit, computer cables, etc.
- Pinpoints shorts and ground faults
- Does not interfere with sensitive electronic equipment



### FEATURES

**UPC/DCI:** 0 95969 36628 1  
**Instruction Manual:** [Yes](#)  
**Hi-Resolution Image:** [Yes](#)

### SPECIFICATIONS

<b>Traces energized wires without power interruption:</b>	9-300 V AC/DC
<b>Locates breakers without power interruption:</b>	9-300 V AC/DC
<b>Traces unenergized wires (wire continuity and wire grounded at the end):</b>	T-100 Transmitter and 9V batteries
<b>Pinpoints shorts and ground faults:</b>	T-100 Transmitter and 9V batteries
<b>Sensitivity settings:</b>	3

### OPTIONAL ACCESSORIES

Part Number	Description
<a href="#">600CKA</a>	Voltage Converter Transformer

### REPLACEMENT PARTS (supplied with product)

Part Number	Description
T100	<i>no description</i>
P100	<i>no description</i>
<a href="#">CC-100</a>	Carrying Case CT-100
PC326	<i>no description</i>
<a href="#">PT 26</a>	Pigtail Connectors
<a href="#">AD-1</a>	CT - 326 Type Adapter
<a href="#">3AG-312.250</a>	Fuse For T-100 and T-300

Country: United States of America  
[Click here to change.](#)