

Electrical Construction Supplies

Ground Rod Clamps & Fittings

Threaded bronze couplings and steel driving studs for use with sectional type Cop-R-Coat ground rods for deep grounding. Cast bronze clamps U/L listed. Stainless steel clamps are recommended to maximize the service life of this grounding system.

**Cast Bronze
8058**



**Bronze Coupling
8535**



**Driving Stud
19535**



**Galvanized
7912**



Catalog No.	Type	Rod Size (inches)	Wire Size (inches)		Std. Pkg.	Wt. Per 100
			Min.	Max.		
8038	Cast Bronze	3/8	14 Sol.	4 Str.	100	7
8012	Cast Bronze	1/2	10 Sol.	2 Str.	100	15
8012SP Economy	Cast Bronze	1/2	10 Sol.	2 Str.	100	15
8058	Cast Bronze	5/8	8 Sol.	1 Str.	100	18
8058SP Economy	Cast Bronze	5/8	10 Sol.	2 Str.	100	11
8034	Cast Bronze	3/4	8 Sol.	1/0 Str.	100	25
8034SP Economy	Cast Bronze	3/4	10 Sol.	2 Str.	100	20
8067	Cast Bronze	5/8 - 3/4	2 Sol.	3/0 Str.	50	40
9067	[304] Stainless	5/8 - 3/4	10 Sol.	2/0	25	50
8010	Cast Bronze	1	8 Sol.	4/0 Str.	25	50

Catalog No	Fitting Type	Size (inches)	Std. Pkg.	Wt. Per 100
8534	Bronze Coupling	5/8	10	30
8535	Bronze Coupling	3/4	10	46
8536	Bronze Coupling	1	10	100
19534	Driving Stud	5/8	10	23
19535	Driving Stud	3/4	10	35
19536	Driving Stud	1	10	75

Copper Connectors

Split Bolt Connector-OC/OPW

Copper connectors expand and contract at the same rate as the conductor for uniformly tight connections. Meets NEMA Standard requirements for mechanical strength.

**Accommodates 3 wires of maximum size.

Connectors and lugs are packed in convenient cartons for handling and resale.

**Split Bolt
Connector-OC**



**Split Bolt
Connector-OPW**



Catalog No.	Maximum Conductor Size		Carton	Std. Pkg. Qty.	Wt. per 100
	Solid	Strand			
10-C	10	10	50	200	1 1/2
8-C	8	8	50	200	3
6-C	6	8	25	100	6
**6-C3	6	8	25	100	7
**4-C	4	6	25	100	9
4-C3	4	6	25	100	10
2-C	2	4	10	40	11
1-C	1	2	5	20	14
0-C	2/0	1/0	10	40	21
2/0-C	3/0	2/0	-	25	26 1/2
3/0-C	4/0	3/0	-	10	37
4/0-250-C	-	250 MCM	-	10	36
350-C	-	350 MCM	-	10	73
500-C	-	500 MCM	-	5	95
750-C	-	750 MCM	-	5	158
* 1000-C	-	1000 MCM	-	2	341

Catalog No.	Maximum Conductor Sizes						Carton Qty.	Std. Pkg.	Wt. per 100
	Copper		Steel		Aluminum				
	Solid	Str.	3-Str.	Guy (inches)	Al. Cable	ACSR			
6-PW	6	8	-	-	6 Sol.	-	25	100	7
4-PW	4	6	8	-	4 Sol.	6	25	100	9
2-PW	2	4	6	1/4	2 Sol.	4	10	40	12
1-PW	1	2	4	5/16	1 Sol.	2	5	20	15
0-PW	2/0	1/0	-	3/8	1/0 Str.	1	10	40	22
2/0-PW	3/0	2/0	-	7/16	2/0 Str.	1/0	-	25	27 1/2
3/0-PW	-	3/0	-	7/16	3/0 Str.	2/0	-	10	48
4/0-PW	-	4/0	-	1/2	4/0 Str.	3/0	-	10	85
350-PW	-	350 MCM	-	21/32	350 MCM	300 MCM	-	10	130
500-PW	-	500 MCM	-	-	500 MCM	447 18/1	-	5	150
750-PW	-	750 MCM	-	-	700 MCM	666.6	-	5	200
1000-PW	-	1000 MCM	-	-	1000 MCM	900	-	2	310