

Incandescent PAR Lamps

| Watts | Shape | Volts | Part # | Description | Initial Lumens | Finish | Filament Type | Length (in.) | Diameter (in.) | Life Hours | Base | Pack By |
|-------|-------|-------|--------|-------------------------------------|----------------|--------|---------------|--------------|----------------|------------|----------------------|---------|
| 8 | PAR36 | 6 | 01669G | PAR36 H7551 6V (PK X 12) | 550 | Clear | C-6 | 2.75 | 4.5 | 50 | Screw Terminals | 12 |
| 8 | PAR36 | 12 | 01679G | PAR36 H7555 12V (PK X 12) SIL | 550 | Clear | C-6 | 2.75 | 4.5 | 50 | Screw Terminals | 12 |
| 12 | PAR36 | 6 | 01675G | PAR36 H7553 6V (PK X 12) | 850 | Clear | C-6 | 2.75 | 4.5 | 50 | Screw Terminals | 12 |
| 12 | PAR36 | 12 | 01670G | PAR36 H7557 12V (PK X 12) | 850 | Clear | C-6 | 2.75 | 4.5 | 50 | Screw Terminals | 12 |
| 18 | PAR36 | 13 | 01683G | PAR36/4414 SEAL BEAM/18W 13V PKX60 | 1500 | Clear | C-6 | 2.75 | 4.5 | 300 | Screw Terminals | 60 |
| 25 | PAR36 | 12 | 01107G | 25PAR36/VWFL 12V (PK X 12) | 150 | Clear | C-6 | 2.75 | 4.5 | 2000 | Screw Terminals | 12 |
| 30 | PAR36 | 13 | 01667G | PAR36 4405 12.8V (PK X 12) | 50000 | Clear | C-6 | 2.75 | 4.5 | 100 | Screw Terminals | 12 |
| 60 | PAR36 | 36 | 01612G | PAR36 4350 SEALED BEAM 36V (PK X12) | 2100 | Clear | C-2V | 2.75 | 4.5 | 400 | Slip-on Terminals | 12 |
| 80 | PAR36 | 48 | 01677G | PAR36 4340 SEALED BEAM 48V(PK X 12) | 2500 | Clear | C-2V | 2.75 | 4.5 | 400 | Screw Terminals | 12 |
| 175 | PAR38 | 125 | 01613 | 175PAR38 HEAT/CLEAR 120V (PK X 12) | | Clear | C-9 | 5.3 | 4.75 | 5000 | Medium Skirted (E26) | 12 |
| 250 | PAR38 | 120 | 01625S | 250PAR38/CAP/SPL/FL30 120V(PKX6) | 3600 | Clear | CC-8 | 5.31 | 4.75 | 4500 | Medium Skirted (E26) | 6 |

Decorative Incandescent Lamps

| Watts | Shape | Volts | Part # | Description | Initial Lumens | Finish | Filament Type | Length (in.) | Diameter (in.) | Life Hours | Base | Pack By |
|-------|--------|-------|----------|-----------------------------------|----------------|---------|---------------|--------------|----------------|------------|------------------|---------|
| 25 | F10.5 | 120 | 01805 | 25F10 1/2 MED 120V SILICONE(PKX4) | 300 | Clear | CC-8 | 4.4 | 1.3 | 3000 | Medium (E26) | 4 |
| 40 | F15 | 120 | 01817S | 40F15/CL 120V (PK X 24) | 422 | Clear | C-7A | 4.5 | 1.88 | 1500 | Medium (E26) | 24 |
| 40 | F15 | 120 | 01806S | 40F15/CL SILICONE (PK X 24) | 422 | Clear | C-7A | 4.5 | 1.88 | 1500 | Medium (E26) | 24 |
| 40 | B9.5 | 130 | 01822SAT | 40B9.5/CL 130V SIL (PK X 25) | 384 | Clear | CC-V2 | 3.5 | 1.1875 | 2500 | Candelabra (E12) | 25 |
| 40 | B11 | 130 | 01823SAT | 40B11 130V SIL (PK X 25) | 360 | Frosted | CC-V2 | 3.88 | 1.375 | 2500 | Medium (E26) | 25 |
| 60 | F15 | 120 | 01808 | 60F15/CL/LL 120V (PK X 24) | 660 | Clear | C-9 | 4.5 | 1.88 | 2000 | Medium (E26) | 24 |
| 60 | F15 | 120 | 01809 | 60F15/CL/LL 120V (PK X 12) | 660 | Clear | C-9 | 4.5 | 1.88 | 2000 | Medium (E26) | 12 |
| 60 | F15 | 120 | 01807 | 60F15/CL/LL SILICONE (PK X 12) | 660 | Clear | C-9 | 4.5 | 1.88 | 2000 | Medium (E26) | 12 |
| 60 | BA10.5 | 130 | 01821I | 60TM/TC/BX 130V (PK X 25) | 220 | Clear | CC2 | 3.75 | 0 | 3000 | Medium (E26) | 25 |

Other Incandescent Lamps

| Watts | Shape | Volts | Part # | Description | Initial Lumens | Finish | Filament Type | Length (in.) | Diameter (in.) | Life Hours | Base | Pack By |
|-------|--------|-------|--------|---------------------------------|----------------|---------|---------------|--------------|----------------|------------|--------------------|---------|
| 7.5 | S11 | 130 | 01033I | 7 1/2 S11/MED 130V (PK X 25) | 40 | Clear | C-7A | 2.25 | 0 | 1500 | Medium (E26) | 25 |
| 15 | S11 | 120 | 01037G | 15S11 CL 120V (PK X24) | 120 | Clear | C-7A | 2.25 | 1.38 | 400 | Medium (E26) | 24 |
| 20 | T6 1/2 | 130 | 01013I | 20T6 1/2 CL/INT (PK X 25) | 150 | Clear | C-8 | 5.5 | 0 | 2000 | Intermediate (E17) | 25 |
| 25 | T10 | 130 | 01004I | 25T10/CL 130V (PK X 6) | 180 | Clear | C-5 | 5.63 | 1.25 | 2000 | Medium (E26) | 6 |
| 25 | T20 | 130 | 01034S | 25T6 1/2 CL 130V (PK X 60) | 242 | Clear | C-8 | 5.5 | 0.81 | 1000 | Intermediate (E17) | 60 |
| 40 | G25 | 120 | 02003G | 40G25 W 120V (PK X 24) | 370 | White | C-6 | 4.5 | 3.13 | 1500 | Medium (E26) | 24 |
| 40 | T10 | 130 | 01005I | 40T10/CL 130V (PK X 6) | 260 | Clear | c-5 | 5.63 | 1.25 | 2000 | Medium (E26) | 6 |
| 40 | T20 | 120 | 01036S | 40T6.5 CL 120V (PK X 6) | 365 | Clear | C-8 | 5.5 | 0.81 | 1000 | Intermediate (E17) | 6 |
| 40 | T6 1/2 | 120 | 01042G | 40T6 1/2 FROST (PK X 60) | 420 | Frosted | C-8 | 5.5 | 0.81 | 750 | Intermediate (E17) | 60 |
| 60 | T10 | 120 | 01003 | 60T10/CL 120V (PK X 24) | 520 | Clear | C-8 | 5.63 | 1.25 | 1000 | Medium (E26) | 24 |
| 150 | PS25 | 130 | 01531I | 150PS25/IF/5M 130V (PK X 60) | 1650 | Frosted | C-9 | 6.81 | 0 | 5000 | Medium (E26) | 60 |
| 165 | P25 | 130 | 01527G | 1950P25/L/TS (PK X 60) | 1950 | Clear | C-9 | 4.75 | 3.13 | 8000 | Medium (E26) | 60 |
| 200 | PS30 | 130 | 01511S | 200PS30 IF/RS 130V (PK X 60) | 3080 | Frosted | C-9 | 8.06 | 3.75 | 1000 | Medium (E26) | 60 |
| 200 | PS25 | 130 | 01530I | 200PS25/IF/5M 130V (PK X 60) | 2400 | Frosted | C-9 | 6.81 | 0 | 5000 | Medium (E26) | 60 |
| 300 | PS30 | 120 | 01512 | 300M/PS30/IF 120-130V (PK X 60) | 6100 | Frosted | C-9 | 8.06 | 3.75 | 750 | Medium (E26) | 60 |
| 300 | PS35 | 120 | 01513 | 300PS35 IF 120-130V (PK X 12) | 5700 | Frosted | C-9 | 9.38 | 4.4 | 1000 | Mogul (E39) | 12 |
| 300 | PS35 | 130 | 01514S | 300PS35 IF 130V (PK X 24) | 5250 | Frosted | C-9 | 9.38 | 4.38 | 1000 | Mogul (E39) | 24 |
| 300 | PS30 | 130 | 01520S | 300PS30M CL 130V (PK X 60) | 5820 | Clear | C-9 | 8.06 | 3.75 | 750 | Medium (E26) | 60 |
| 300 | PS25 | 130 | 01525I | 300M/PS25/IF/99 130V (PK X 60) | 3595 | Frosted | C-9 | 6.81 | 0 | 5000 | Medium (E26) | 60 |