

01124E

40A15/IF 230-250V (PK X 25)

Application: Offices, Schools,
Restaurants, Medical, Retail,
Hospitality, General Lighting

Average Life Hours: 1500

Base: Medium (E26)

Bulb: A15

Coating: Silicone

CRI: 100

Diameter: 1.90 IN

Finish: Inside Frost

Initial Lumens: 435

Pack By: 25

Weight: 0.100

Length: 3.50 IN

Mean Lumens: 435

Package Dimensions: 6.00 x
7.80 x 10.30

Package Weight: 2.40 L

Shape: A15

Special Features: Shatter-
Resistant

Type: Incandescent

UNSPSC: 39101612

UPC: 726585011247

Volts: 230-250

Warranty URL: [Download
Warranty](#)

Wattage: 40.0

