

# 01411S

150A23 IF/RS 130V (PK X 48)

**Application:** Rough & Vibration Service, General Lighting

**Average Life Hours:** 1000

**Base:** Medium (E26)

**Bulb:** A23

**Coating:** PFA

**Kelvin:** 2850

**CRI:** 100

**Diameter:** 2.88 IN

**Finish:** Inside Frost

**Initial Lumens:** 2090

**Pack By:** 48

**Weight:** 0.116

**Length:** 6.06 IN

**Mean Lumens:** 2090

**SDS:** [Download SDS](#)

**Package Dimensions:** 15.25 x 8.75 x 19.50

**Package Weight:** 6.00 L

**Shape:** A23

**Special Features:** Shatter-Resistant

**Type:** Incandescent

**UNSPSC:** 39101612

**UPC:** 726585014118

**Volts:** 130

**Warranty URL:** [Download Warranty](#)

**Wattage:** 150.0



APPROVED