

01696W

250R40/HT/CLEAR (PK X 2)

Application: Offices, Schools, Restaurants, Medical, Retail, Hospitality, General Lighting

Average Life Hours: 5000

Base: Medium (E26)

Bulb: R40

Coating: PFA

Kelvin: 2700

CRI: 100

Diameter: 5.00 IN

Finish: Clear

Initial Lumens: 1200

Pack By: 2

Weight: 0.442

Length: 6.50 IN

SDS: [Download SDS](#)

Package Dimensions: 6.00 x 7.80 x 10.30

Package Weight: 1.15 L

Shape: R40

Special Features: Shatter-Resistant

Type: Incandescent

UNSPSC: 39101612

UPC: 726585016969

Volts: 120

Warranty URL: [Download Warranty](#)

Wattage: 250.0

