

# 81040S

FB40T12/CWX/6 (PK X 12)

**Application:** Industrial, Food Processing, Food Service, Retail, Hospitality, General Lighting

**Average Life Hours:** 21000

**Base:** Medium Bi-Pin (G13)

**Bulb:** T12

**Coating:** Copolymer

**Color:** Cool White

**Kelvin:** 4100

**CRI:** 87

**Diameter:** 1.50 IN

**Initial Lumens:** 2100

**Pack By:** 12

**Weight:** 0.958

**Length:** 22.50 IN

**Mean Lumens:** 1806

**SDS:** [Download SDS](#)

**Package Dimensions:** 10.50 x 16.25 x 24.25

**Package Weight:** 10.05 L

**Shape:** U-Bent

**Special Features:** Shatter-Resistant

**Type:** Curvalume Fluorescent Lamp

**UNSPSC:** 39101605

**UPC:** 726585810406

**Warranty URL:** [Download Warranty](#)

**Wattage:** 40.0

