

90502S

M175 BU/ED28 (PK X 6)

Application: Offices, Schools.
Restaurants, Medical, Retail,
Hospitality, General Lighting

Average Life Hours: 10000

Ballast Type: M57/E

Base: Mogul (E39)

Beam Angle: 360

Bulb: ED28

Coating: PFA

Kelvin: 4200

CRI: 65

Diameter: 3.50 IN

Finish: Clear

Initial Lumens: 14400

Pack By: 6

Length: 8.30 IN

Light Center Length: 5 IN

Mean Lumens: 9300

SDS: [Download SDS](#)

Package Dimensions: 12.25 x
14.25 x 15.25

Package Weight: 3.80 L

Shape: ED28

Special Features: Shatter-
Resistant

Type: Metal halide lamp HID

UNSPSC: 39101614

UPC: 726585905027

Warranty URL: [Download
Warranty](#)

Wattage: 175.0

