

90804S

M400 BU/ED37 (PK X 6)

Application: Offices, Schools.
Restaurants, Medical, Retail,
Hospitality, General Lighting

Average Life Hours: 20000

Ballast Type: M59/S

Base: Mogul (E39)

Beam Angle: 360

Bulb: ED37

Coating: PFA

Kelvin: 4000

CRI: 65

Diameter: 4.60 IN

Finish: Clear

Initial Lumens: 36000

Pack By: 6

Length: 11.50 IN

Light Center Length: 7 IN

Mean Lumens: 23500

SDS: [Download SDS](#)

Package Dimensions: 12.25 x
9.50 x 14.25

Package Weight: 4.75 L

Shape: ED37

Special Features: Shatter-
Resistant

Type: Metal halide lamp HID

UNSPSC: 39101614

UPC: 726585908042

Warranty URL: [Download
Warranty](#)

Wattage: 400.0

