

93501S

MP175 IF/BU (PK X 6)

Application: Offices, Schools.
Restaurants, Medical, Retail,
Hospitality, General Lighting

Average Life Hours: 10000

Ballast Type: M57/O

Base: Exclusionary Mogul
(EX39)

Bulb: BT28

Coating: PFA

Kelvin: 3800

CRI: 70

Diameter: 3.50 IN

Initial Lumens: 12800

Pack By: 6

Length: 8.31 IN

Light Center Length: 5 IN

Mean Lumens: 7800

SDS: [Download SDS](#)

Package Dimensions: 12.25 x
10.00 x 13.75

Package Weight: 5.85 L

Shape: BT28

Special Features: Shatter-
Resistant

Type: Metal halide lamp HID

UNSPSC: 39101614

UPC: 726585935017

Volts: 132

Warranty URL: [Download
Warranty](#)

Wattage: 175.0

