

97309

HPS100 ALTO (PK X 12)

Application: Roadway, Parking Lots, Security Lighting, Landscape Lighting, Building Washes

Average Life Hours: 24000

Base: Mogul (E39)

Bulb: ED23 1/2

Coating: PFA

Kelvin: 2100

CRI: 21

Diameter: 2.13 IN

Initial Lumens: 10000

Pack By: 12

Weight: 0.500

Length: 7.75 IN

Light Center Length: 5 IN

Mean Lumens: 8460

SDS: [Download SDS](#)

Package Dimensions: 9.00 x 12.25 x 16.00

Package Weight: 5.65 L

Shape: ED23 1/2

Special Features: Shatter-Resistant

Type: High pressure sodium lamp HID

UNSPSC: 39101617

UPC: 726585973095

Volts: 55

Warranty URL: [Download Warranty](#)

Wattage: 100.0

