

# 97800

HPS400 ALTO (PK X 12)

**Application:** Roadway, Parking Lots, Security Lighting, Landscape Lighting, Building Washes

**Average Life Hours:** 24000

**Base:** Mogul (E39)

**Bulb:** ED18

**Coating:** PFA

**Kelvin:** 2100

**CRI:** 21

**Diameter:** 2.25 IN

**Initial Lumens:** 50000

**Pack By:** 12

**Weight:** 0.483

**Length:** 9.75 IN

**Light Center Length:** 5.75 IN

**Mean Lumens:** 45000

**SDS:** [Download SDS](#)

**Package Dimensions:** 12.25 x 8.00 x 10.50

**Package Weight:** 5.70 L

**Shape:** ED18

**Special Features:** Shatter-Resistant

**Type:** High pressure sodium lamp HID

**UNSPSC:** 39101617

**UPC:** 726585978007

**Volts:** 100

**Warranty URL:** [Download Warranty](#)

**Wattage:** 400.0

