



93600S

MP250 BU (PK X 6)



Application: Offices, Schools, Restaurants, Medical, Retail, Hospitality, General Lighting

Ballast Type: M58/O

Bulb: BT28

Color Temperature: 4000 K

Diameter: 3.50 IN

Initial Lumens: 23000

Length: 8.31 IN

Mean Design Lumens: 17000

Package Weight: 4.00 L

Shape: BT28

Type: Metal halide lamp HID

Voltage: 133 V

Average Life Hours: 17000

Base: Exclusionary Mogul (EX39)

Coating: PFA

CRI: 65

Effective Arc Length: 1

Lamp Type: Metal Halide

Light Center Length: 5 IN

Package (LxWxH): 13.75 IN x 10.00 IN x 12.25 IN

Pack By: 6

Special Features: Shatter-Resistant

UPC: 726585936007

Wattage: 250.0 W

ULEPH,ROHS,NSF Splash Zone