



Dependable Power for Any Application

# Product Datasheet

## 120 X 240 Primary Volts - 16/32 Secondary Volts - 1Ø Buck-Boost Transformer - Single Phase

Catalog #: T181054



### PRODUCT FEATURES

- UL listed, CSA certified
- UL Type 3R epoxy encapsulated
- Single or Three Phase Applications
- Wall Mounted
- Covered under Acme's 10 year limited warranty

---

### BENEFITS

- Easily configured for numerous applications
- Lower cost solution
- 5-10 times increase in kVA

---

### UL STANDARD

UL 506

---

### CSA STANDARD

C22.2 No 47

---

### WARRANTY

Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

---

### GENERAL PRODUCT INFORMATION

VA: 50  
kVA: -

Primary Voltage:	120 X 240
Secondary Voltage:	16/32
Frequency:	50/60 Hz
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

#### PRODUCT MEASUREMENTS

Height (In./cm):	6.41 (16.3)
Width (In./cm):	3.14 (8.0)
Depth (In./cm):	3.05 (7.7)

#### CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall

#### PACKAGING

Ship Weight (Lbs/Kg):	4 (1.8)
-----------------------	---------

#### COMPLIANCES

UL Standard:	UL 506
UL Listed:	File E79947
CSA Standard:	C22.2 No 47
CSA Listed:	LR7357-26
Warranty:	Acme Electric Warranty Card
	<a href="http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf">www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf</a>