



Representative

**Catalog Number:** AL24  
**Product ID:** 7TAA268500R0009  
**UPC Number:** 78378604732  
**Status:** Active

Aluminum Two-Hole Lug - Straight Long Barrel, Wire Range 397 30/7, 26/7, 18/1, 477 18/1 ASCR, 450-500 Stranded, 600 kcmil, 1/2 Inch Bolt Size, Blind-End, Hydraulic Dies: 106H, CSA 28, B20AH, EEI 14A, 318, 1 5/16

### North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Blackburn
Type	Compression Connector
Special Features	PreFilled with Compound. Complete Die and Crimp information clearly indented on each lug. Installed with standard tools and dies. Use 1/2 inch mounting hardware for all sizes.
Application	For Aluminum and Copper Conductor.
Cable Size	397 30/7, 26/7, 18/1, 477 18/1 ASCR, 450-500 Stranded, 600 kcmil
Number Of Holes	2
Material	Aluminum
Mounting	NEMA Standard Mounting Holes
Connection	Crimp

### European Specifications (ETIM)

ETIM	EC001053 Crimp cable lug for aluminium conductors
Material	Aluminium
Number of fixing holes	2
Sleeve form	Long

### Packaging

Outer Quantity	20
Outer Dimensions (inches)	11.7x11.4x3.9
Weight Uom	72 lbs. per 100

### Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)