



Representative

Catalog Number: CSP40
Product ID: 7TAH007500R0039
UPC Number: 78378613211
Status: Active

Type CSP Copper Splice, Short Barrel, Max 35kV, Wire Size 4/0 Str, Tin Plated, Die Color Code Purple

- Made of high-conductivity seamless copper tubing. Tin plated for corrosion resistance.
- Specifically chamfered barrel for ease of installation.
- Color-coded for matching die identification.

North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Blackburn
Type	Short Barrel Copper Splice
Special Features	Made of high-conductivity seamless copper tubing. Tin plated for corrosion resistance.
Standard	UL E9809
Conductor Range	4/0 Str
Material	Copper
Finish	Tin Plated
Color	Purple
Voltage Rating	35KV

Packaging

Inner Quantity	10
Inner Dimensions (inches)	3.3x2.8x2.3
Outer Quantity	100
Outer Dimensions (inches)	4.2x4.2x3.2
Weight Uom	9 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com