



Actual

Catalog Number: K656DR
Product ID: 7TAA122230R0008
UPC Number: 78378663626
EAN Number: 05415022249347
Status: Active

600Amp, 15/25kV, 600 Series Deadbreak Insulated Cap with Test Point (with Stud)

North American Specifications (UNSPSC)

UNSPSC	26121630 Cable accessories
IGCC	1779 Cable accessories
Brand Name	Elastimold
Type	Insulated Cap
Special Features	15/28 kV, 600 Amp Deadbreak Rated. Molded EPDM Rubber. Provision for ground wire connection. Provision for hotstick operation.
Application	The insulated cap is designed to insulate, shield, and water seal 15/28kV, 600 Amp IEEE Std. 386 bushing interfaces. Units have a capacitance test point which can be used to check if the system is energized. A threaded stud attachment is standard.
Standard	ANSI/IEEE Standard 386
Size	3.13 inch (79.4 mm) Diameter of Cable Entrance, 8.31 inch (211.1 mm) Length
Material	EPDM Rubber

Packaging

Outer Quantity	1
Outer Dimensions (inches)	50
Weight Uom	1.9 lbs. Each

Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com