



Actual



Family

**Catalog Number:** AMTD50044  
**Product ID:** 7TAH006400R0082  
**UPC Number:** 78378650312  
**Status:** Active

AMT 4 Multi-Port Both Sides PVC Connector, Ultraviolet Resistant, Wire Range 500 kcmil-4 Str, Length 5.26 Inches, Width 3.0 Inches, Height 2.75 Inches, Hex Size 3/8 Inch, Black Insulation

- PVC Insulation eliminates insulation failures and reduces outage costs. Removable port and screw plugs.
- Compact design provides space efficiencies.
- All cable entry are equipped with an anti-oxidation compound.

### North American Specifications (UNSPSC)

UNSPSC	39121410 Terminal blocks
IGCC	4547 Terminal blocks
Brand Name	Blackburn
Type	AMT Connectors
Special Features	PVC Insulation eliminates insulation failures and reduces outage costs. Removable port and screw plugs.
Standard	UL E9809
Wire Size	500 kcmil-4 Str
Voltage Rating	600V
Material	Aluminum
Color	Black

### Packaging

Outer Quantity	10
Outer Dimensions (inches)	13.187x7.75x7
Weight Uom	1.3 lbs. Each

### Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email:techsupport@tnb.com