

# INDESTRUCTIBLE Lantern

LED

**RAYOVAC**



**LIFETIME  
WARRANTY**

**530** | **15** foot (4m)  
LUMENS | DROP TESTED



VIRTUALLY  
**INDESTRUCTIBLE**

- **530 Lumen High Performance LED**

- 3 light modes: High, Medium and Low
- 360 meter beam distance

- **Lifetime Warranty**

- 15-Foot Drop Tested
- Aluminum-titanium body
- 100% Waterproof/Submersible (ANSI IPX7)
- Over-mold rubber head
- Shatterproof lens & reflector
- Impact resisting internal engineering

- **10-Hour Runtime**

- **Includes handy wrist strap**

- **Includes (3) D Alkaline Batteries**

- **100% Recyclable Package**

**SRP:\$29.99**

Model

DIY3DLN-BC