

INDESTRUCTIBLE 6AA Spotlight



- **670 Lumen High Performance LED**
 - 3 light modes: High, Medium and Low
 - 360 meter beam distance
- **Lifetime Warranty**
 - 15-Foot Drop Tested
 - Aluminum-titanium body
 - 100% Waterproof/Submersible (ANSI® IPX7)
 - Over-mold rubber head
 - Shatterproof lens & reflector
 - Impact resisting internal engineering
- 10-Hour Runtime
- Includes handy wrist strap
- Includes (6) AA Alkaline Batteries

34% More Lumens



Model

DIY6AASP-BC